

Eaton EABC26

Eaton Crouse-Hinds series Condulet EAB conduit outlet box with cover, 3" cover opening diameter, Feraloy iron alloy, C shape, 3/4"

General specifications

PRODUCT NAME	Eaton Crouse-Hinds series Condulet EAB conduit outlet box with cover
CATALOG NUMBER	EABC26
UPC	782274247809
PRODUCT LENGTH/DEPTH	5.56 in
PRODUCT HEIGHT	3.75 in
PRODUCT WIDTH	2.78 in
PRODUCT WEIGHT	4 lb

Certifications and compliances

AREA CLASSIFICATION	Hazardous/Classified Locations
STANDARDS TYPE	NEC/CEC
NEC HAZARDOUS RATING	Class I, Division 1 Class I, Division 2 Class II, Division 1 Class II, Division 2 Class III
NEMA RATING	3 4 7 9

Product specifications

SHAPE	C
TRADE SIZE	3/4"
COVER OPENING DIAMETER	3"
MATERIAL	Feraloy iron alloy

Resources

CATALOGS	Crouse-Hinds series EAB and EAB ATEX Conduit Outlet Boxes catalog page
CERTIFICATION REPORTS	Condulet EAB and EAJ Explosionproof Conduit Outlet Boxes UL certification (EAB) Condulet EAB and EAJ Explosionproof Conduit Outlet Boxes Canadian certification (EAB)
INSTALLATION INSTRUCTIONS	IF 1472 - EAB Condulet Conduit Outlet Bodies IF 1730 - GUA/EAB/EAJ Condulet Outlet Boxes
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - EABC26
TECHNICAL SERVICE BULLETINS	Industrial Fittings Bend Radius and Cubic Capacity Chart

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

Follow us on social media to get the latest product and support information.



© 2025 Eaton. All Rights Reserved.