



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



EABY16 1/2" 4HUB Cond Body & CVR

Crouse-Hinds

Catalog Number	EABY16
Manufacturer	Crouse-Hinds
Description	Eaton Crouse-Hinds Series Condulet Eab Conduit Outlet Box With Cover, 3" Cover Opening Diameter, Feraloy Iron Alloy, Y Shape, 1/2"
Weight per unit	4.6 (lbs/each)
Product Category	Bodies & Covers

Features

Cable Entry	(4) Side, (1) Down
dimensions	5.3100 IN X 2.5300 IN X 4.5300 IN
Material	FERALOY IRON ALLOY

Dimensions and Weight

Size	1/2 in
------	--------

Descriptions

Description	1/2" 4HUB COND BODY & CVR
extra long description	CRS-H EABY16 1/2 Y IRON GRP AB ROUN
Features	Crouse-Hinds series EAB and EAJ explosionproof conduit outlet boxes are installed in conduit systems in hazardous areas to protect conductors in threaded rigid conduit, act as pull and splice boxes, change conduit direction, and provide access to conductors for maintenance and future system changes.EAB and EAJ outlet boxes are manufactured in five different hub configurations with mounting feet and 16 pitch cover threads.
Long Description	Eaton Crouse-Hinds series Condulet EAB conduit outlet box with cover, 3" cover opening diameter, Feraloy iron alloy, Y shape, 1/2"
Product Type	1/2 Y Iron GRP Ab Round Base Outlet CVR
Special Features	With Cover

Manufacturer Information

Brand	Eaton
GTIN	00782274248905
Manufacturers Part Number	EABY16
UPC	782274248905

Taxonomies, Classifications, and Categories

Category Description	HUB STYLE BOXES (GUAB, GUAT, ETC)
Type	Conduit outlet box with cover



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Weight Per each	4.6299

Uses, Certifications, and Standards

Application	Ind Facilities & Factories - Industrial Facilities/Factories - Other
standard	UL 886, CSA C22.2