

Eaton ECL03A1A3A

Catalog Number: ECL03A1A3A

CN35 or A202 Enclosed Lighting Contactor, Non-combination electrically held, 10A, Painted steel NEMA 1 enclosure, 110V/50 Hz, 120V/60 Hz coil, Three-pole, 45 mm frame



Photo is representative

General specifications

Product Name	Catalog Number
Eaton CN35 electrically held lighting contactor	ECL03A1A3A
	UPC
	782114189849
Product Length/Depth	Product Height
5.62 in	9.51 in
Product Width	Product Weight
5.71 in	5.2 lb
Warranty	Certifications
Eaton Selling Policy 25-000, one (1) year cUL Listed from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	UL Listed
	Catalog Notes
	Ampere rating is based on a maximum load voltage of 480V for tungsten lamp applications and 600V for ballast or mercury vapor type applications

defaultTaxonomyAttributeLabel

Amperage Rating

10A

Number Of Poles

Three-pole

Type

Non-combination electrically held

Coil voltage

110-120 Vac, 50/60 Hz

Enclosure

NEMA 1

Enclosure material

Painted steel

Frame size

45 mm

Resources

Brochures

[Lighting contactors](#)

Catalogs

[Eaton's Volume 10—Enclosed Control](#)

Multimedia

[S1. E4. Ask the Experts - NEMA, IEC and DP contactors](#)

Specifications and datasheets

[Eaton Specification Sheet - ECL03A1A3A](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)