

# Eaton ECN1641CAJ

Catalog Number: ECN1641CAJ

Eaton Freedom NEMA enclosed control , 220V/50 Hz-240V/60 Hz , NEMA 1 , Combination non-reversing starter—circuit breaker , HAND/OFF/AUTO selector switch , Three-phase



Photo is representative

## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton Freedom NEMA enclosed control	ECN1641CAJ
<b>UPC</b>	<b>Product Length/Depth</b>
782114040195	8.44 in
<b>Product Height</b>	<b>Product Width</b>
30.5 in	20.5 in
<b>Product Weight</b>	<b>Warranty</b>
90 lb	1 year

## Certifications

UL Listed file E1491

Contact Manufacturer

## defaultTaxonomyAttributeLabel

### Coil voltage

440V/50 Hz-460V/60 Hz

### Enclosure

NEMA 1

### Type

Combination non-reversing starter—circuit breaker

### Circuit breaker rating

250A

### Phase

Three-phase

### Size

NEMA size 4

## Resources

### Catalogs

[Eaton's Volume 10—Enclosed Control](#)

### Specifications and datasheets

[Eaton Specification Sheet - ECN1641CAJ](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://Eaton.com/socialmedia)