

# Eaton ECNR30

Catalog Number: ECNR30

Eaton Edison ECNR fuse, Time-delay current-limiting fuse, Superior overload and cycling capabilities, 30 A, Dual, Class RK5, Non-indicating, Ferrule end x ferrule end, 8 sec at 500%, 200 kAIC, Standard, 250 V, 125 Vdc

## General specifications

Product Name	Catalog Number
Eaton Edison ECNR fuse	ECNR30
UPC	Product Length/Depth
782634507345	8.5 in
Product Height	Product Width
2.35 in	2.35 in
Product Weight	Warranty
1.84 lb	Not Applicable
Compliances	
CE Marked	

## Electrical rating

### Amperage Rating

30 A

### Interrupt rating

200 kAIC

### Response time

8 sec at 500%

### Voltage rating

250 Vac, 125 Vdc

## Physical details

### Number of elements

Dual

### Packaging type

Standard

## General information

### Class

Class RK5

### Fuse indicator

Non-indicating

### Special features

Non current limiting

## Resources

### Catalogs

[Edison full line catalog 1005](#)

### Multimedia

[Bussmann series Fuseology](#)

### Specifications and datasheets

[Eaton Specification Sheet - ECNR30](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)