

Specifications

Photo is representative

Eaton ECP123608

Eaton Crouse-Hinds series ECP enclosure, Square cover, 8-15/16" depth, 12" x 36" x 8", Copper-free aluminum, Tap-in mounting feet

Certifications and compliances

AREA CLASSIFICATION	Hazardous Locations
STANDARDS TYPE	NEC/CEC
NEC HAZARDOUS RATING	Class I, D Class I, D Class II, E Class II, F Class III
NEMA RATING	3 3R 4 7 9

General specifications

PRODUCT NAME	Eaton Crouse-Hinds series ECP enclosure
CATALOG NUMBER	ECP123608
UPC	662276322042
PRODUCT LENGTH/DEPTH	17 in
PRODUCT HEIGHT	41.05 in
PRODUCT WIDTH	11.92 in
PRODUCT WEIGHT	247 lb



Powering Business Worldwide

Specifications

Photo is representative

Eaton ECP123608

Eaton Crouse-Hinds series ECP enclosure, Square cover, 8-15/16" depth, 12" x 36" x 8", Copper-free aluminum, Tap-in mounting feet

Certifications and compliances

AREA CLASSIFICATION	Hazardous Locations
STANDARDS TYPE	NEC/CEC
NEC HAZARDOUS RATING	Class I, Div 1 Class I, Div 2 Class II, Div 1 Class II, Div 2 Class III
NEMA RATING	3 3R 4 7 9

General specifications

PRODUCT NAME	Eaton Crouse-Hinds series ECP enclosure
CATALOG NUMBER	ECP123608
UPC	662276322042
PRODUCT LENGTH/DEPTH	17 in
PRODUCT HEIGHT	41.05 in
PRODUCT WIDTH	11.92 in
PRODUCT WEIGHT	247 lb



Powering Business Worldwide