

Specifications

Photo is representative

Eaton ECP242408

Eaton Crouse-Hinds series ECP enclosure, Square cover, 9-7/16" depth, 24" x 24" x 8", Copper-free aluminum, Tap-in mounting feet

Certifications and compliances

AREA CLASSIFICATION	Hazardous Locations
STANDARDS TYPE	NEC/CEC
NEC HAZARDOUS RATING	Class I, D Class I, D Class II, E Class II, F Class III
NEMA RATING	3 3R 4 7 9

General specifications

PRODUCT NAME	Eaton Crouse-Hinds series ECP enclosure
CATALOG NUMBER	ECP242408
UPC	662276321984
PRODUCT LENGTH/DEPTH	29.33 in
PRODUCT HEIGHT	29.33 in
PRODUCT WIDTH	12.53 in
PRODUCT WEIGHT	279 lb



Powering Business Worldwide

Specifications

Photo is representative

Eaton ECP242408

Eaton Crouse-Hinds series ECP enclosure, Square cover, 9-7/16" depth, 24" x 24" x 8", Copper-free aluminum, Tap-in mounting feet

Certifications and compliances

AREA CLASSIFICATION	Hazardous Locations
STANDARDS TYPE	NEC/CEC
NEC HAZARDOUS RATING	Class I, D Class I, D Class II, E Class II, F Class III
NEMA RATING	3 3R 4 7 9

General specifications

PRODUCT NAME	Eaton Crouse-Hinds series ECP enclosure
CATALOG NUMBER	ECP242408
UPC	662276321984
PRODUCT LENGTH/DEPTH	29.33 in
PRODUCT HEIGHT	29.33 in
PRODUCT WIDTH	12.53 in
PRODUCT WEIGHT	279 lb



Powering Business Worldwide