



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2250 West Broadway Road Suite 102
85202-0000, AZ Mesa
Phone: 623-900-2983
Fax: 623-900-2984



EDGW1RM6 Led Exit Surf MNT Edge-Lit WHT Red LTR SNGL Face

Lithonia Lighting - Acuity

Catalog Number	EDGW1RM6
Manufacturer	Lithonia Lighting - Acuity
Description	Surface Mount Led Edge-Lit, White, Single Face, Red, Sku - 144ffa
Weight per unit	4.4 (lbs/each)
Product Category	Exit Signs

Features

battery	4.8 volts
Fixture Type	Exit Sign
Hardware	No
Lamp Included	Yes
Lamp Type	LED - Static
Material	Aluminum
Number of Lamps	1
Power Source	Hardwired
Shape	Square
Voltage Rating	120,277 V
Warranty	5
Wattage	3

Material, Color, and Finish

Background Color	White
Color	White
Finish	Gloss
housing color	White
Lens Material	Acrylic
Letter Color	RED

Dimensions and Weight

Height	11.75
Length	13.75
Width	1.625



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2250 West Broadway Road Suite 102
85202-0000, AZ Mesa
Phone: 623-900-2983
Fax: 623-900-2984

Descriptions

Description	LED EXIT SURF MNT EDGE-LIT WHT RED LTR SNGL FACE
extra long description	LITH EDG W 1 R M6 Surface mount LED
Long Description	Surface mount LED edge-lit, White, Single face, Red, SKU - 144FFA
Product Type	Emergency Exit Sign
Special Features	The versatile EDG/EDGR edge-lit exits are well suited for any application requiring attractive edge-lit exit signage. Typical installations include commercial spaces such as retail, offices or medical facilities but can be applied in any space where an upgraded appearance is desired.

Manufacturer Information

Brand	Lithonia Lighting
GTIN	00745974508533
Manufacturers Part Number	EDG W 1 R M6
UPC	745974508533

Taxonomies, Classifications, and Categories

Category Description	Emergency & Exit Lighting
Type	Exit Sign

Packaging

Carton	1
Package	6
Weight Per each	4.44

Uses, Certifications, and Standards

Application	Education,Government,Healthcare,Hospitality,Offices & Banks,Retail
environmental conditions	Indoor,Outdoor
Mounting	SURFACE
standard	NFPA 101,NFPA 70,UL