

Eaton EDSC271 SA

Catalog Number: EDSC271 SA

Eaton Crouse-Hinds series FlexStation EDS back box, Copper-free aluminum, Single-gang, Through feed, 3/4"

General specifications

| | |
|--|----------------|
| Product Name | Catalog Number |
| Eaton Crouse-Hinds series FlexStation EDS back box | EDSC271 SA |
| | UPC |
| | 782274871158 |
| Product Length/Depth | Product Height |
| 5 in | 8.2 in |
| Product Width | Product Weight |
| 3.7 in | 2.45 lb |



Certifications and compliances

Area classification

Hazardous/Classified Locations

Standards type

NEC/CEC

NEC hazardous rating

Class II, Division 2

Class III

Class I, Division 2

Class I, Zone 2

Class I, Division 1

Class II, Division 1

Class I, Zone 1

NEMA Rating

7

3R

12

9

Product specifications

Number of gangs

Single-gang

Style

Through feed

Trade size

3/4"

Material

Copper-free aluminum

Resources

Catalogs

[FlexStation Explosionproof Control Station Components catalog page](#)

Certification reports

[FlexStation Explosionproof Control Station Components UL certification](#)

[FlexStation Explosionproof Control Station Components UL certification \(Components\)](#)

[FlexStation Explosionproof Control Station Components Canadian certification](#)

Installation instructions

[IF 1928 - FlexStation Series Control Stations](#)

[IF 1418 - FlexStation Series Control Stations](#)

[IF 1358 - Replacing Plastic Buttons on EDS Series](#)

[IF 899 - EDSX, EDS, EFS, DSDX and DSD Control Stations](#)

Specifications and datasheets

[Eaton Specification Sheet - EDSC271 SA](#)