



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



EGE3020FFG E 3P 20A 25KA Fixed Thermal Fixed Mag Single Pack

Eaton Corp

Catalog Number	EGE3020FFG
Manufacturer	Eaton Corp
Description	Eaton Series G Complete Molded Case Circuit Breaker. 3P 20A 25KA, Fixed, Thermo Magnetic, Single Pack
Weight per unit	2.8 (lbs/each)
Product Category	3 Pole Interchangeable Trip TH

Features

Current Rating	20 A
dimensions	2.9902 IN X 3.0000 IN X 5.5000 IN
frame	EG
media	Yes
Poles	3
Voltage Rating	600Y/347 Vac

Descriptions

Description	E 3P 20A 25KA FIXED THERMAL FIXED MAG SINGLE PACK
extra long description	ETN EGE3020FFG E 3P 20A 25KA FIXED
Features	The Eaton Series G Molded Case Circuit Breaker provides users with unparalleled performance and convenience. A patented contact design features high-speed "blow-open" action, resulting in superior circuit breaker performance. This globally-rated platform offers users high interruption ratings in a compact footprint with ease of in-field configuration applicable to a wide variety of industry and regional requirements. Choose from a selection of thermal magnetic and electronic trip units, available in curren
Long Description	Eaton Series G complete molded case circuit breaker. 3P 20A 25kA, fixed, thermo magnetic, single pack
Product Type	E 3P 20A 25KA Fixed TM Single PK CB

Manufacturer Information

Brand	EATON CUTLER-HAMMER
GTIN	00782116131389
Manufacturers Part Number	EGE3020FFG
UPC	782116131389

Taxonomies, Classifications, and Categories

Category Description	MOLDED CASE BREAKERS
Type	Molded case circuit breaker



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Weight Per each	2.7799

Uses, Certifications, and Standards

Application	Elec Assemblies, Panels & OEM - Electrical Assemblies and EOEMs - Other
standard	IEC Rated,UL Listed,CSA Certified,CE Marked,RoHS conform