



Powering Business Worldwide

pe.eaton.com

Standby Generator

EGENA22

UPC:786679163894

Dimensions:

- **Height:** 29 IN
- **Length:** 48 IN
- **Width:** 25 IN

Weight:476 LB

Warranties:

- 5 year

Specifications:

- **Type:** Generator
- **Accessories:** Fascia Base Wrap Kit
- **Display:** LCD
- **Enclosure Material:** Aluminum
- **Frequency Rating:** 50-60 Hz
- **Number Of Cylinders:** 2
- **Rated Control Supply Voltage:** 120/240V
- **Phase:** Single-phase
- **Wattage:** 19.5 kW, 22 kW

Supporting documents:

- [Eaton Specification Sheet - EGENA22](#)

Certifications:

- UL 2200
- UL 1008
- UL 67
- cUL Listed
- CSA Certified

Product compliance:

- SCAQMD compliance





Powering Business Worldwide

pe.eaton.com

Standby Generator

EGENA22

UPC:786679163894

Dimensions:

- **Height:** 29 IN
- **Length:** 48 IN
- **Width:** 25 IN

Weight:476 LB

Warranties:

- 5 year

Specifications:

- **Type:** Generator
- **Accessories:** Fascia Base Wrap Kit
- **Display:** LCD
- **Enclosure Material:** Aluminum
- **Frequency Rating:** 50-60 Hz
- **Number Of Cylinders:** 2
- **Rated Control Supply Voltage:** 120/240V
- **Phase:** Single-phase
- **Wattage:** 19.5 kW, 22 kW

Supporting documents:

- [Eaton Specification Sheet - EGENA22](#)

Certifications:

- UL 2200
- UL 1008
- UL 67
- cUL Listed
- CSA Certified

Product compliance:

- SCAQMD compliance

