

Eaton EGL210 J1 J3

Catalog Number: EGL210 J1 J3

Eaton Crouse-Hinds series EGL static grounding indicator, 10A/15A, Copper-free aluminum, One red and one green pilot light, 120 Vac

General specifications

Product Name	Catalog Number
Eaton Crouse-Hinds series EGL static grounding indicator	EGL210 J1 J3
	UPC
	782274784960
Product Length/Depth	Product Height
11.07 in	12.8 in
Product Width	Product Weight
8.41 in	32 lb

Certifications and compliances

Area classification

Hazardous/Classified Locations

Standards type

NEC/CEC

NEC hazardous rating

Class I, Division 1

Class I, Zone 1

Class I, Division 2

Class I, Zone 2

Class II, Division 1

Class II, Division 2

Class III

NEMA Rating

3

4X

7

9

12

Product specifications

Amperage Rating

10A/15A

Voltage rating

120 Vac

Material

Copper-free aluminum

Type

One red and one green pilot light

Resources

Catalogs

[EGL Series Explosionproof Static Grounding Indicators catalog page](#)

Certification reports

[EGL Explosionproof Static Grounding Indicators Canadian certification](#)

[EGL Explosionproof Static Grounding Indicators UL certification](#)

Installation instructions

[IF 1879 - EGL-M6 Grounding Indicators with Automatic Pump Control](#)

[IF 1512 - EGL Grounding Indicators with Automatic Pump Control](#)

Specifications and datasheets

[Eaton Specification Sheet - EGL210 J1 J3](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)