



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## EM3728 1/4 HP 1075 RPM 208/230V Ball Bearing Shaft 1/2"X6

*Precision Electric Motor*

Catalog Number	EM3728
Manufacturer	Precision Electric Motor
Description	60 Hertz Frequency Rating; UI, Csa Approval; Condenser Fan Application; 208 to 230 Volt Ac 1-Phase Voltage Rating; Extended Stud Mounting; 11 Pound Weight; 1/4 HP Power Rating; 1075 RPM Speed Rating; Teao Enclosure Type; Steel Frame Material; B Insulation Class; 1.8 to 2 Amp Motor Fla; Yes Reversible; 1 Service Factor; 48 Nema Frame Size; Economaster[R] Brand; Type Induction Run, Permanent Split Capacitor; Shaft Type Double Flat; Bearing Type Ball (Drive End); Number Of Poles 6; Overall Dimension 5.6 Inch
Weight per unit	11.0 (lbs/each)
Product Category	20190723150303

### Descriptions

Description	1/4 HP 1075 RPM 208/230V BALL BEARING SHAFT 1/2"X6
Long Description	60 HERTZ FREQUENCY RATING; UL, CSA APPROVAL; CONDENSER FAN APPLICATION; 208 TO 230 VOLT AC 1-PHASE VOLTAGE RATING; EXTENDED STUD MOUNTING; 11 POUND WEIGHT; 1/4 HP POWER RATING; 1075 RPM SPEED RATING; TEAO ENCLOSURE TYPE; STEEL FRAME MATERIAL; B INSULATION CLASS; 1.8 TO 2 AMP MOTOR FLA; YES REVERSIBLE; 1 SERVICE FACTOR; 48 NEMA FRAME SIZE; ECONOMASTER[R] BRAND; TYPE INDUCTION RUN, PERMANENT SPLIT CAPACITOR; SHAFT TYPE DOUBLE FLAT; BEARING TYPE BALL (DRIVE END); NUMBER OF POLES 6; OVERALL DIMENSION 5.6 INCH
Product Type	Motor Capacitor Mounting Kit

### Manufacturer Information

Brand	
GTIN	00786674019554
Manufacturers Part Number	87256001
UPC	786674019554

### Taxonomies, Classifications, and Categories

Category Description	Generic HAVCR Motors
----------------------	----------------------

### Packaging

Carton	1
Weight Per each	11