



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## EM3729 1/3 HP 1075 RPM 208/230V Ball Bearing Shaft 1/2"X6

*Precision Electric Motor*

Catalog Number	EM3729
Manufacturer	Precision Electric Motor
Description	60 Hertz Frequency Rating; UI, Csa Approval; Condenser Fan Application; 208 to 230 Volt Ac 1-Phase Voltage Rating; Extended Stud Mounting; 14 Pound Weight; 1/3 HP Power Rating; 1075 RPM Speed Rating; Teao Enclosure Type; Rolled Steel Frame Material; B Insulation Class; 2.2 to 2.5 Amp Motor Fla; Yes Reversible; 1 Service Factor; 48 Nema Frame Size; Economaster[R] Brand; Type Induction Run, Permanent Split Capacitor; Shaft Type Double Flat; Bearing Type Ball (Drive End); Number Of Poles 6; Overall Dimension
Weight per unit	14.0 (lbs/each)
Product Category	20190723150251

### Descriptions

Description	1/3 HP 1075 RPM 208/230V BALL BEARING SHAFT 1/2"X6
Long Description	60 HERTZ FREQUENCY RATING; UL, CSA APPROVAL; CONDENSER FAN APPLICATION; 208 TO 230 VOLT AC 1-PHASE VOLTAGE RATING; EXTENDED STUD MOUNTING; 14 POUND WEIGHT; 1/3 HP POWER RATING; 1075 RPM SPEED RATING; TEAO ENCLOSURE TYPE; ROLLED STEEL FRAME MATERIAL; B INSULATION CLASS; 2.2 TO 2.5 AMP MOTOR FLA; YES REVERSIBLE; 1 SERVICE FACTOR; 48 NEMA FRAME SIZE; ECONOMASTER[R] BRAND; TYPE INDUCTION RUN, PERMANENT SPLIT CAPACITOR; SHAFT TYPE DOUBLE FLAT; BEARING TYPE BALL (DRIVE END); NUMBER OF POLES 6; OVERALL DIMENSION
Product Type	Centrifugal Blower

### Manufacturer Information

Brand	
GTIN	00786674019561
Manufacturers Part Number	50747-D401
UPC	786674019561

### Taxonomies, Classifications, and Categories

Category Description	Generic HAVCR Motors
----------------------	----------------------

### Availability

Status	Inactive
--------	----------

### Packaging

Carton	1
Weight Per each	14