



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## EML28 Lug Kit - 2 Cable Connection For 290 MM Soft Start

Eaton Corp

Catalog Number	EML28
Manufacturer	Eaton Corp
Description	Eaton It Soft Starter Accessory, Terminal Kit, #107-250 Kcmil, 2 Cable Connections, Frame V
Weight per unit	4.3 (lbs/each)
Product Category	Starter Accessories

### Features

media	Yes
-------	-----

### Dimensions and Weight

Depth	7.5
Height	4
Width	4.5

### Descriptions

Description	LUG KIT - 2 CABLE CONNECTION FOR 290 MM SOFT START
extra long description	ETN EML28 LUG KIT-2 CBL CONNECTION
Features	Advanced intelligence. Compact footprint. The S811+/S801+ line of intelligent technologies soft starters is designed to be the smallest, most compact soft starter in the market today. With this small size, it can easily fit in place of existing soft starter designs, wye-delta starters or across-the-line NEMA and IEC starters. This feature allows easy retrofits of existing motor control centers or enclosures and saves the expense of replacing existing structures or adding a new one to house a soft starter.
Long Description	Eaton IT soft starter accessory, Terminal kit, #107-250 kcmil, 2 cable connections, Frame V
Product Type	Lug Kit-2 CBL Connection For 290 MM RVSS

### Manufacturer Information

Brand	EATON CUTLER-HAMMER
GTIN	00782114665510
Manufacturers Part Number	EML28
UPC	782114665510

### Taxonomies, Classifications, and Categories

Category Description	CONTROLLERS
----------------------	-------------

### Packaging

Carton	1
Weight Per each	4.26



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Uses, Certifications, and Standards

Application

Commercial / Institutional Buildings / Structures - Power

Distribution and Controls

standard

CSA Certified