

May 1, 2000
Supersedes all previous



E.M.T. Standard and Special Radius Elbows*

Galvanized E.M.T. 90°-45° Elbows

NOTE: Weights shown are approximate for 90° elbows. To arrive at weights for 60° elbows deduct 10%, for 45° elbows deduct 15% and for 30° elbows deduct 20%.

Size	List Price per 100 Pieces	90°	45°	60°	30°	Carton Quantity	Approx. Weight per 100 Pieces (lbs)
½"	198.84	02021▲	02031■	02041■	02051■	50	28
¾"	200.13	02022▲	02032■	02042■	02052■	50	46
1"	261.47	02023▲	02033▲	02043■	02053■	25	86
1½"	378.10	02024▲	02034▲	02044■	02054■	25	148
1½"	493.17	02025▲	02035▲	02045■	02055■	20	198
2"	752.53	02026▲	02036▲	02046■	02056■	10	286
2½"	1832.22	02027▲	02037▲	02047■	02057■	Bulk	536
3"	2731.81	02028▲	02038▲	02048■	02058■	Bulk	720
3½"	3661.51	02029▲	02039■	02049■	02059■	Bulk	1080
4"	4307.69	02030▲	02040▲	02050■	02060■	Bulk	1333

PREFIX: EMTELB (SIZE) (DEGREE)

E.M.T. Special Radius Elbows*

All E.M.T. Special Radius Elbows are **NON-CANCELABLE** and **NON-RETURNABLE**

Size	List Price Each	15" Radius				App. Wt. (lbs.)	Size	List Price Each	18" Radius				App. Wt. (lbs.)
		90°	45°	60°	30°				90°	45°	60°	30°	
1½"						1½"							
1½"	31.55	02206●	●			4	1½"	33.99	02131●	●	●	●	4
2"							2"	40.09	02132●	●	●	●	6
2½"	52.60	02207●	●				2½"	61.21	02133●	●	●	●	
							3"						
							3½"	96.58	02134●	●	●	●	
Size	List Price Each	24" Radius				App. Wt. (lbs.)	Size	List Price Each	30" Radius				App. Wt. (lbs.)
		90°	45°	60°	30°				90°	45°	60°	30°	
1½"	34.06	02092●	●	●	●	5	1½"						
1½"	44.83	02093●	●	●	●	5	1½"						
2"	49.13	02094●	02209●	●	●	7	2"	57.74	02102●	02210●	●	●	8
2½"	72.74	02095●	02095●	●	●	11	2½"						
3"	86.73	02096●	●	●	●	13	3"	102.03	02104●	●	●	●	14
3½"	127.15	02097●	●	●	●		3½"	158.95	02105●	●	●	●	19
4"	135.10	02098●	●	●	●	17	4"	152.75	02106●	●	●	●	21
Size	List Price Each	36" Radius				App. Wt. (lbs.)	Size	List Price Each	42" Radius				App. Wt. (lbs.)
		90°	45°	60°	30°				90°	45°	60°	30°	
1½"							1½"						
1½"	55.64	02109●	●	●	●	7	1½"						
2"	66.42	02110▲	●	●	●	9	2"						
2½"	90.93	02111■	●	●	●	13	2½"						
3"	119.73	02112●	●	●	●	16	3"						
3½"	166.09	02113●	●	●	●	22	3½"						
4"	166.74	02114▲	02212●	●	●	24	4"	203.87	02122●	02213●	●	●	28
Size	List Price Each	48" Radius				App. Wt. (lbs.)	PREFIX: EMTELB (SIZE)(DEGREE)(RADIUS)						
		90°	45°	60°	30°		Availability Codes						
1½"							Stock = ▲						
1½"	68.80	23222●	●	●	●	9	5 Days = ■						
2"	83.43	02126●	●	●	●	12	10 Days = ●						
2½"													
3"	150.21	02128●	●	●	●	21							
3½"	209.20	02129●	●	●	●	28							
4"	232.49	02130▲	02214●	●	●	31							

*UL Listed & Labeled
Reference page 14 for approximate dimensions.

*Note: All EMT can be made to the same dimensions as Rigid - Call the factory

Products on this page without UPC codes are currently being assigned UPC identification by NEMA. Information was not available at this time for printing.



ECN KORN'S

ROBROY INDUSTRIES

ELBOWS

- Galvanized
- EMT
- IMC
- Aluminum

COUPLINGS

- Galvanized
- Aluminum

CLAMPS

The Original
"KORN'S CLAMP"

- Right Angle (RA)
Conduit Supports
- Edge Type (ET)
Conduit Supports
- J-Clamps
- One Hole Straps
- Clampback Spacers
- U-Bolts
- SS Hardware
- Parallels (PAR)
- Beam Clamps

NIPPLES

- Galvanized
- Aluminum

MANUFACTURERS UPC #784011

Price List
Catalog F-162

Effective May 1, 2000
Supercedes all previous

Revised: 3-22-2001

Dimensional and Material Specifications where applicable:
Underwriters' Laboratories No. 6 A.N.S.I. C80.1, Fed. Specs. WW-C-581e

May 1, 2000
Supersedes all previous



E.M.T. Standard and Special Radius Elbows*

**Galvanized E.M.T.
90°-45° Elbows**

NOTE: Weights shown are approximate for 90° elbows. To arrive at weights for 60° elbows deduct 10%, for 45° elbows deduct 15% and for 30° elbows deduct 20%.

Size	List Price per 100 Pieces	Degree				Carton Quantity	Approx. Weight per 100 Pieces (lbs)
		90°	45°	60°	30°		
½"	198.84	02021▲	02031■	02041■	02051■	50	28
¾"	200.13	02022▲	02032■	02042■	02052■	50	46
1"	261.47	02023▲	02033▲	02043■	02053■	25	86
1½"	378.10	02024▲	02034▲	02044■	02054■	25	148
1½"	493.17	02025▲	02035▲	02045■	02055■	20	198
2"	752.53	02026▲	02036▲	02046■	02056■	10	286
2½"	1832.22	02027▲	02037▲	02047■	02057■	Bulk	536
3"	2731.81	02028▲	02038▲	02048■	02058■	Bulk	720
3½"	3661.51	02029▲	02039■	02049■	02059■	Bulk	1080
4"	4307.69	02030▲	02040▲	02050■	02060■	Bulk	1333

PREFIX: EMTELB (SIZE) (DEGREE)

E.M.T. Special Radius Elbows*

All E.M.T. Special Radius Elbows are NON-CANCELABLE and NON-RETURNABLE

Size	List Price Each	15" Radius				App. Wt. (lbs.)	Size	List Price Each	18" Radius				App. Wt. (lbs.)
		90°	45°	60°	30°				90°	45°	60°	30°	
1½"						1½"							
1½"	31.55	02206●	●			4	1½"	33.99	02131●	●	●	●	4
2"							2"	40.09	02132●	●	●	●	6
2½"	52.60	02207●	●				2½"	61.21	02133●	●	●	●	
							3"						
							3½"	96.58	02134●	●	●	●	
Size	List Price Each	24" Radius				App. Wt. (lbs.)	Size	List Price Each	30" Radius				App. Wt. (lbs.)
		90°	45°	60°	30°				90°	45°	60°	30°	
1½"	34.06	02092●	●	●	●	5	1½"						
1½"	44.83	02093●	●	●	●	5	1½"						
2"	49.13	02094●	02209●	●	●	7	2"	57.74	02102●	02210●	●	●	8
2½"	72.74	02095●	02095●	●	●	11	2½"						
3"	86.73	02096●	●	●	●	13	3"	102.03	02104●	●	●	●	14
3½"	127.15	02097●	●	●	●		3½"	158.95	02105●	●	●	●	19
4"	135.10	02098●	●	●	●	17	4"	152.75	02106●	●	●	●	21
Size	List Price Each	36" Radius				App. Wt. (lbs.)	Size	List Price Each	42" Radius				App. Wt. (lbs.)
		90°	45°	60°	30°				90°	45°	60°	30°	
1½"							1½"						
1½"	55.64	02109●	●	●	●	7	1½"						
2"	66.42	02110▲	●	●	●	9	2"						
2½"	90.93	02111■	●	●	●	13	2½"						
3"	119.73	02112●	●	●	●	16	3"						
3½"	166.09	02113●	●	●	●	22	3½"						
4"	166.74	02114▲	02212●	●	●	24	4"	203.87	02122●	02213●	●	●	28
Size	List Price Each	48" Radius				App. Wt. (lbs.)	Availability Codes						
		90°	45°	60°	30°		Stock = ▲	5 Days = ■	10 Days = ●				
1½"													
1½"	68.80	23222●	●	●	●	9							
2"	83.43	02126●	●	●	●	12							
2½"													
3"	150.21	02128●	●	●	●	21							
3½"	209.20	02129●	●	●	●	28							
4"	232.49	02130▲	02214●	●	●	31							

PREFIX: EMTELB (SIZE)(DEGREE)(RADIUS)

*UL Listed & Labeled
Reference page 14 for approximate dimensions.

*Note: All EMT can be made to the same dimensions as Rigid - Call the factory

Products on this page without UPC codes are currently being assigned UPC identification by NEMA. Information was not available at this time for printing.



ECN KORN'S

ROBROY INDUSTRIES

ELBOWS

- Galvanized
- EMT
- IMC
- Aluminum

COUPLINGS

- Galvanized
- Aluminum

CLAMPS

The Original
"KORN'S CLAMP"

- Right Angle (RA)
Conduit Supports
- Edge Type (ET)
Conduit Supports
- J-Clamps
- One Hole Straps
- Clampback Spacers
- U-Bolts
- SS Hardware
- Parallels (PAR)
- Beam Clamps

NIPPLES

- Galvanized
- Aluminum

MANUFACTURERS UPC #784011

Price List
Catalog F-162

Effective May 1, 2000
Supercedes all previous

Revised: 3-22-2001

Dimensional and Material Specifications where applicable:
Underwriters' Laboratories No. 6 A.N.S.I. C80.1, Fed. Specs. WW-C-581e