



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



EN1260RAR 60W E Trans.120V-12V 60W *Wac Lighting CO.,*

Catalog Number	EN1260RAR
Manufacturer	Wac Lighting CO.,
Description	UL & CUL Listed Electronic Transformer Is The Perfect Solution For Wiring Multiple Low Voltage Fixtures. Wac Transformers Are Intrinsically Safer Transformers Because They Are Compartmentalized to Allow No Greater Than 5 Amps Of Current to Be Drawn On Each Compartment. Secondary Wiring For Transformers Do Not Require Conduit Sheathed Cable or Clamp Wiring Techniques. This Transformer Has A Low Minimum Load Requirement Of 1W to Allow The Use Of Led Products. May Be Dimmed Using An Electronic Low Voltage Dim
Weight per unit	0.1300 (lbs/each)
Product Category	Lighting

Features

Category	Track
Safety Rating	UL/ETL
Voltage	120.00 FT

Material, Color, and Finish

Finish	BLACK GLOSS
Style	Traditional

Descriptions

Description	60W E TRANS.120V-12V 60W
Long Description	UL & cUL listed electronic transformer is the perfect solution for wiring multiple low voltage fixtures. WAC transformers are intrinsically safer transformers because they are compartmentalized to allow no greater than 5 amps of current to be drawn on each compartment. Secondary wiring for transformers do not require conduit sheathed cable or clamp wiring techniques. This transformer has a low minimum load requirement of 1W to allow the use of LED products. May be dimmed using an electronic low voltage dim
Product Type	Transformer

Manufacturer Information

Brand	Wac Lighting CO.,
GTIN	00790576094595
Manufacturers Part Number	EN-1260-R-AR
UPC	790576094595



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description	Led Lighting
Type	Parts

Packaging

Carton	1
Weight Per each	0.13