



**On-Q**  
**14-inch Enclosure with Screw-On Cover**  
Part No. EN1400



This 14" On-Q enclosure is the perfect solution for a basic structured wiring system. It features larger top openings that make pulling wire easier as well as additional knockouts, more side lances, and side tabs for more flexible mounting. It includes

## Features & Benefits

14-in Enclosure with Screw-On Cover

Drywall depth indicators

Flush and surface installation

Mounting tabs provide correct flush-mount position for standard installations

Patented mounting system offers versatile module mounting options

Cover included

Made in the USA

## Specifications

### General Info

Product Line	On-Q	Color	White
UPC Number	804428023012	Country Of Origin	United States
Material	Steel	Application Sector	Residential
Standard	UL (UL985, UL1023, UL1863), cULus, CSA, RoHS	Type	Enclosure

### Dimensions

Product Width US	14.25 in	Product Depth US	3.6 in
Product Height US	14.0 in	Enclosure Size	14 in

### Listing Agencies / 3rd Party Agencies

---

CSA Listed

Yes

cULus Listed

Yes

---

### Additional Information

---

RoHS Compliant

Yes

---

### Technical Information

---

Thickness

0.1 in

Cable Entry

(6) rear knockouts

---

Frame

Cold Rolled Steel

---



**On-Q**  
**14-inch Enclosure with Screw-On Cover**  
Part No. EN1400



This 14" On-Q enclosure is the perfect solution for a basic structured wiring system. It features larger top openings that make pulling wire easier as well as additional knockouts, more side lances, and side tabs for more flexible mounting. It includes

## Features & Benefits

14-in Enclosure with Screw-On Cover

Drywall depth indicators

Flush and surface installation

Mounting tabs provide correct flush-mount position for standard installations

Patented mounting system offers versatile module mounting options

Cover included

Made in the USA

## Specifications

### General Info

Product Line	On-Q	Color	White
UPC Number	804428023012	Country Of Origin	United States
Material	Steel	Application Sector	Residential
Standard	UL (UL985, UL1023, UL1863), cULus, CSA, RoHS	Type	Enclosure

### Dimensions

Product Width US	14.25 in	Product Depth US	3.6 in
Product Height US	14.0 in	Enclosure Size	14 in

## Listing Agencies / 3rd Party Agencies

---

CSA Listed

Yes

cULus Listed

Yes

---

### Additional Information

---

RoHS Compliant

Yes

---

### Technical Information

---

Thickness

0.1 in

Cable Entry

(6) rear knockouts

---

Frame

Cold Rolled Steel

---