



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



ESV10BXQ Stronghold™ ESV10BX-Q Butt Panduit Corporation

Catalog Number	ESV10BXQ
Manufacturer	Panduit Corporation
Description	Stronghold ESV10BX-Q Contractor Grade Vinyl Insulated Butt Splices Are A Reliable and Economical Option That Withstand A Wide Range Of General-Purpose Applications. They Are Designed to Splice Two Solid or Stranded Wires Together to Repair or Lengthen Wires. Accommodates 12-10 Awg, Are Yellow In Color, and Come In Packages Of 25.
Weight per unit	0.0500 (lbs/each)
Product Category	Small Terminals & Connectors

Features

connection	Expanded
insulation	Vinyl
Material	Copper
Wire Size	12 - 10 AWG

Material, Color, and Finish

Color	Yellow
Finish	Tin-Plated

Descriptions

Description	STRONGHOLD™ ESV10BX-Q BUT
extra long description	PAN ESV10BX-Q StrongHold™ ESV10BX-Q
Long Description	StrongHold ESV10BX-Q Contractor Grade Vinyl Insulated Butt Splices are a reliable and economical option that withstand a wide range of general-purpose applications. They are designed to splice two solid or stranded wires together to repair or lengthen wires. Accommodates 12-10 AWG, are yellow in color, and come in packages of 25.
Product Type	Stronghold™ ESV10BX-Q Butt Splice, Yellow, Vinyl, 1.22", 12-

Manufacturer Information

Brand	Panduit Corporation
GTIN	00074983279784
Manufacturers Part Number	ESV10BX-Q
UPC	074983279784

Taxonomies, Classifications, and Categories

Category Description	TERMINALS
Type	Butt Splice



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	25
Package	250
Weight Per each	0.05

Uses, Certifications, and Standards

Mounting	0.31
standard	UL Listed, CSA Certified