



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## ESV14BXL 16-14AWG Blue Insld Butt Splice *Panduit Corporation*

|                  |  |
|------------------|--|
| Catalog Number   | ESV14BXL   |
| Manufacturer     | Panduit Corporation  |
| Description      | Stronghold™ Butt Splice, Vinyl Insulated, 16 - 14 Awg, Blue. |
| Weight per unit  | 0.1000 (lbs/each)  |
| Product Category | Small Terminals & Connectors                                 |

### Features

|            |           |
|------------|-----------|
| connection | Expanded  |
| insulation | Vinyl     |
| Material   | Copper    |
| media      | Yes       |
| Wire Size  | 16-14 AWG |

### Material, Color, and Finish

|        |        |
|--------|--------|
| Color  | Blue   |
| Finish | Tinned |

### Descriptions

|                        |  |
|------------------------|--|
| Description            | 16-14AWG BLUE INSLTD BUTT SPLICE                             |
| extra long description | PAN ESV14BX-L StrongHold™ ESV14BX-L                          |
| Long Description       | StrongHold™ Butt Splice, Vinyl Insulated, 16 - 14 AWG, Blue. |
| Product Type           | Stronghold™ ESV14BX-L Butt Splice                            |

### Manufacturer Information

|                           |                |
|---------------------------|----------------|
| Brand                     | Panduit®       |
| GTIN                      | 00074983279814 |
| Manufacturers Part Number | ESV14BX-L      |
| UPC                       | 074983279814   |

### Taxonomies, Classifications, and Categories

|                      |             |
|----------------------|-------------|
| Category Description | TERMINALS   |
| Type                 | Butt Splice |

### Packaging

|                 |     |
|-----------------|-----|
| Carton          | 50  |
| Package         | 500 |
| Weight Per each | 0.1 |

### Uses, Certifications, and Standards

|          |                          |
|----------|--------------------------|
| Mounting | 0.31                     |
| standard | UL Listed, CSA Certified |