



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



ET2825C 2-Circ 365/7 Astro Elec Timer Indoor Metal Encls *Intermatic Inc.*

Catalog Number	ET2825C
Manufacturer	Intermatic Inc.
Description	Astronomic 7-Day/365 Day 2-Circuit Electronic Control, 120-277 Vac, 2-SPST/DPST, Indoor Metal Enclosure
Weight per unit	2.8 (lbs/each)
Product Category	Electronic Time Switches

Features

action	2 x SPST
amperage rating	30
connection	Wire Lead
Contact Configuration	1 NO
Contact Rating	30 AMP @ 120/240 VAC, 20 AMP @ 28 VDC (Resistive), 30 AMP @ 120/240 VAC (Inductive), 5 AMP @ 120/240 VAC (Tungsten), 20 AMP @ 120 - 277 VAC, 10 AMP @ 120/277 VAC (Ballast)
motor power	1 HP @ 120 VAC, 2 HP @ 240 VAC
Poles	1
Timing Range	1 MIN - 6 DAYS 23 HR 59 MIN
Voltage Rating	120 - 277
Wire Size	#18 - #10



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

Description	2-CIRC 365/7 ASTRO ELEC TIMER INDOOR METAL ENCLS
extra long description	INT-MAT ET2825C Astronomic 7-Day/36
Features	The ET2000 Series offers an easy-to-use interface, while still allowing to-the-minute scheduling capabilities for nearly any application. This series provides 50 holiday blocks with independent scheduling to ensure the loads are always in the proper ON/OFF state. This series also includes 96 ON/OFF events for even the most demanding schedules. The scheduling capabilities, configurable outputs, and a 100-hour backup without the need of batteries, make this series ideal for nearly any application.
Long Description	Astronomic 7-Day/365 Day 2-Circuit Electronic Control, 120-277 VAC, 2-SPST/DPST, Indoor Metal Enclosure
Product Type	Astronomic 7-Day/365 Day 2-Circuit Electronic Control, 120-2
Special Features	Features: Automatic Voltage Detection for Fast, Easy, Out-of-the-Box Installations, Control Different Load Types and Voltages from a Single Control, Adjust Daylight Savings Time Through Software, Rather than DIP Switches, Configurable Outputs Allow These Models to Cover Various Types of Applications with a Single Clock, New Mode of Operation Allows For Manual On/Off Buttons to Operate as a 2-Hour Override, Non-Volatile Eeprom Memory Protects Programming Indefinitely, 2 Year Warranty

Manufacturer Information

Brand	Intermatic
GTIN	00078275147690
Manufacturers Part Number	ET2825C
UPC	078275147690

Taxonomies, Classifications, and Categories

Category Description	TIME CLOCKS
Type	Astronomic Electronic

Packaging

Carton	1
Package	6
Weight Per each	2.75



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application	Exterior Lighting, Interior Lighting, Security Lighting, Parking Lot Lighting, Bell Ringing, Electric Motors, Electric Pump, Indoor
Enclosure	Type 1 Steel
Frequency Rating	50/60
Mounting	WALL MOUNT
Operating Temperature standard	-40 to +155 DEG F, -40 to +68 DEG C
	UL Rating, Meet Title 20/24 Compliance