

Eaton EVLEDC201

Catalog Number: EVLEDC201

Eaton Crouse-Hinds series EV LED light fixture, 0.12A, Cool white, AC drive, 100-200W incan equiv lumin, 50/60 Hz, Heat and impact resistant glass globe, With guard, Copper-free alum, No mounting module, 0.86 power factor, 100-277 Vac, 15W

General specifications



Product Name	Catalog Number
Eaton Crouse-Hinds series EV LED light fixture	EVLEDC201
	UPC 662276273276
Product Length/Depth	Product Height
7.25 in	12.75 in
Product Width	Product Weight
7.25 in	11 lb

Certifications and compliances

Area classification

Hazardous/Classified Locations

Standards type

NEC/CEC

NEC hazardous rating

Class I, Division 1

Class I, Zone 1

Class I, Zone 2

Class II, Division 1

NEMA Rating

4X

Ingress protection (IP) ratings

IP66

Product specifications

Color temperature

Cool white

Mounting Method

No mounting module

Guard

With guard

Drive type

AC

Voltage rating

100-277 Vac

Frequency rating

50/60 Hz

Wattage

15W

Amperage Rating

0.12 A

Power factor

0.86

Material

Copper-free aluminum

Globe material

Heat and impact resistant glass

Equivalent luminaire

100-200W incandescent

Resources

Brochures

[Crouse-Hinds series Global LED lighting portfolio](#)

Catalogs

[Crouse-Hinds series Hazard-Gard EV LED catalog page](#)

Certification reports

[EV LED Explosionproof LED Light Fixtures UL certification \(Marine\)](#)

[EV LED Explosionproof LED Light Fixtures UL certification](#)

[EV LED Explosionproof LED Light Fixtures Canadian certification](#)

Installation instructions

IF 1562 - Hazard-Gard EV LED

Specifications and datasheets

Eaton Specification Sheet - EVLEDC201



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)