



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1620 Highway 155
75803-8616, TX Palestine
Phone: 903-723-2141
Fax: 903-723-1451



EW101B Multivolt 7 Day Supercap Indoor/Outdoor 1 CH. 40a

Nsi Industries

| | |
|------------------|--|
| Catalog Number | EW101B |
| Manufacturer | Nsi Industries |
| Description | Supercap, 7 Day Time Setting Mode, SPST Contact Form, 7 Day Time Setting, 120 to 277 V Ac, 40 A (No) @ 120 to 277 V Ac (General Purpose);30 A (No) @ 120 V Ac;20 A (No) @ 208 to 277 V Ac (Ballast);15 A (No) @ 120 V Ac (Tungsten);30 A @ 28 V DC (Resistive);40 A (No) @ 120 to 277 V Ac (Inductive), 20 On/Off Cycles, Plastic Enclosure Material, Screw Connection, -40 °F Operating Temperature, +149 °F Operating Temperature, 5.062 X 3.062 X 8.312 In Size, 2 LB |
| Weight per unit | 2.0 (lbs/each) |
| Product Category | Electronic Time Switches |

Features

| | |
|----------------|--------------|
| action | SPST |
| Base | Screw |
| Contact Rating | 120-277 VAC |
| Phase | Single Phase |
| Poles | 1 |
| Timing Range | 7 DAY |

Descriptions

| | |
|------------------------|---|
| Description | MULTIVOLT 7 DAY SUPERCAP INDOOR/OUTDOOR 1 CH. 40A |
| extra long description | TORK EW101B 7 Day Digital Timer One |

Manufacturer Information

| | |
|------|----------------|
| GTIN | 00786261824318 |
| UPC | 786261824318 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|------------------------------------|
| Category Description | 1PH MANUAL STARTERS |
| Type | 7 Day Time Switch - 1 Or 2 Channel |

Packaging

| | |
|-----------------|---|
| Carton | 1 |
| Weight Per each | 2 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1620 Highway 155
75803-8616, TX Palestine
Phone: 903-723-2141
Fax: 903-723-1451

Uses, Certifications, and Standards

| | |
|--------------------------|--------------------------------|
| Enclosure | NEMA 3R Plastic Indoor-Outdoor |
| environmental conditions | -40 to + 149 F |
| Frequency Rating | 50-60 Hz |
| Mounting | Screw Mount |
| Operating Temperature | -40 to + 149 F |
| standard | UL917 |