

EASY-WRAP™

Rubber Splicing, Harness Wrap, & Duct Tape

EWRT, EWWH, EWDT SERIES



EASY-WRAP™ RUBBER SPLICING

- High quality unvulcanized rubber that will bond quickly to itself to form a solid mass of watertight protection.
- Self-fusing with liner.
- Can be used as primary insulation for electrical wires and cable splices up to 600 volts.
- Conforms to irregular shapes and is flexible to withstand expansion and contraction.
- Highly resistant to salt water, steam, oils, detergents and other chemicals.

TEMPERATURE RATING:

Dielectric strength 490 Volts per mil.

Meets HH-I-553C Grade B and ASTM D-119; UL 510 listing #2C58.

| CAT. NO. | COLOR | LENGTH (FT.) | WIDTH (IN.) | THICKNESS (IN.) | STD. CTN. QTY. |
|----------------------|-------|--------------|-------------|-----------------|----------------|
| EWRT 3022-.75 | Black | 22 | 0.750 | 0.030 | 1 |
| EWRT 3022-1.5 | Black | 22 | 1.500 | 0.030 | 1 |
| EWRT 3022-2 | Black | 22 | 2.000 | 0.030 | 1 |

EASY-WRAP™ WIRE HARNESS WRAP

- A 5 mil PVC film, coated with a rubber adhesive for high elongation and exceptional adherence.
- Excellent conformability to the wiring harness. Matte finish.



| CAT. NO. | COLOR | LENGTH (FT.) | WIDTH (IN.) | THICKNESS (IN.) | STD. CTN. QTY. |
|------------------|-------|--------------|-------------|-----------------|----------------|
| EWWH 5060 | Black | 60 | 0.750 | 0.005 | 1 |

DUCT TAPE

- Superior cloth duct tapes, designed to meet all industry demands and applications.
- Uniform MD/CD tear properties.



| CAT. NO. | COLOR | TENSILE (IN/LBS.) | LENGTH (YD.) | WIDTH (IN.) | THICKNESS (mm.) | STD. CTN. QTY. |
|---------------|--------|-------------------|--------------|-------------|-----------------|----------------|
| EWDT-8 | Silver | 18 | 55 | 2.000 | 18 | 1 |