



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



EZ14S0 Ez 14 Cu-In. 1G Old Work

Cantex, Inc

Catalog Number	EZ14S0
Manufacturer	Cantex, Inc
Description	1-Gang 14 Cu. In. Ez Box Old Work Residential Electrical Switch and Outlet Box With Ez Mount Clamps and Wire Clamps Gray
Weight per unit	0.2600 (lbs/each)
Product Category	Non-Metallic

Features

Cable Entry	4 integral wire clamps
installation type	Old Work
Material	PVC
Mounting Type	flanges

Material, Color, and Finish

Color	Gray
-------	------

Dimensions and Weight

Size	1-Gang
------	--------

Descriptions

Also Known As...	Cut in box old-work box Old Work Box Retrofit Junction Box Pop-in Box Remodeling box
Construction	old work
Description	EZ 14 CU-IN. 1G OLD WORK
extra long description	CTX EZ14SO 14 CU IN SINGLE GANG OLD
Features	CANTEX EZ14SO EZ BOX is a 1-Gang 14 cu. in. renovation (old work) electrical switch or outlet box is for residential or light commercial renovation (old work) projects when a 1-gang box is needed. EZ mount flanges, winged swing tabs and built in wire clamps make installation easy and cost effective.
Long Description	1-Gang 14 cu. in. EZ BOX Old Work Residential Electrical Switch and Outlet Box with EZ Mount Clamps and Wire Clamps Gray
Product Type	14 Cu In Single Gang Oldwk Box
Special Features	wing tabs



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

Brand	PVC & Accessories
GTIN	00088700019843
Manufacturers Part Number	EZ14SO
sub brand	EZ BOX ®
UPC	088700019843

Taxonomies, Classifications, and Categories

Category Description	PLASTIC BOXES
Type	1-gang low voltage old work switch & outlet box

Packaging

Carton	1
Package	50
Weight Per each	0.26

Uses, Certifications, and Standards

Application	1-gang old work switch & outlet box
Mounting	flanges
standard	UL, 2 hour fire-rated