Elliott Electric Supply

We Deliver...Lower Cost, Quality Products, & Personal Service

110 Success Blvd
79029-0000, TX Dumas
Phone: 806-934-4805
Fax: 806-717-2052



F017841EC0 17W T8 24" 4100K 82 Cri Bi-Pin

Sylvania-Ledvance

Catalog Number	F017841EC0
Manufacturer	Sylvania-Ledvance
Description	17W, 24" Mol, T8 Octron Fluorescent Lamp, 4100K Color Temperature, Rare Earth Phosphor, 82 Cri, Suitable For Is or RS Operation, Ecologic
Weight per unit	0.2400 (lbs/each)
Product Category	Linear Fluorescent Straight La

Features

amperage rating	Ballast Dependent
Base	Medium Bipin
bulb type	T8
Lamp Type	RAPID & INSTANT START
Shape	T8
total harmonic distortion	Ballast Dependent
Voltage Rating	Ballast Dependent
Wattage	17

Material, Color, and Finish

color rendering index (cri)	82
color temperature	4100
Finish	Phosphor Coated

Descriptions

Description	17W T8 24" 4100K 82 CRI BI-PIN
extra long description	LDV FO17841ECO/22137 FO17841ECO 30/
Long Description	17W, 24" MOL, T8 OCTRON fluorescent lamp, 4100K color temperature, rare earth phosphor, 82 CRI, suitable for IS or RS operation, ECOLOGIC

Manufacturer Information

Brand	SYLVANIA
GTIN	00046135221378
Manufacturers Part Number	FO17/841/ECO/22137
UPC	046135221378

Taxonomies, Classifications, and Categories

Category Description	Fluorescent
Type	FLUORESCENT

Packaging

Carton	1
Package	30
Weight Per each	0.24