



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## F032V35ECO 32W T8 48" 3500K 90cri *Sylvania-Ledvance*

Catalog Number	F032V35ECO
Manufacturer	Sylvania-Ledvance
Description	32W, 48 Inch Mol, T8 Octron Vivid Value Fluorescent Lamp Combines Vivid Color Rendering With Entry Level Value, 3500K Color Temperature, Rare Earth Phosphor, 90 Cri, Suitable For Is or PRS Operation, Ecologic .Vivid Color: High Cri Lamps For Color Critical Applications.
Weight per unit	0.4207 (lbs/each)
Product Category	Linear Fluorescent Straight La

### Features

Base	Medium Bipin
bulb type	T8
Lamp Type	RAPID & INSTANT START
lumens	2450
Shape	T8

### Material, Color, and Finish

color rendering index (cri)	90
color temperature	3500

### Descriptions

Description	32W T8 48" 3500K 90CRI
extra long description	SYL FO32V35ECO/22437 FO32V35ECO 30/
Long Description	32W, 48 inch MOL, T8 OCTRON VIVID VALUE fluorescent lamp combines VIVID color rendering with entry level VALUE, 3500K color temperature, rare earth phosphor, 90 CRI, suitable for IS or PRS operation, ECOLOGIC .VIVID Color: High CRI lamps for color critical applications.

### Manufacturer Information

Brand	SYLVANIA
GTIN	00046135224379
Manufacturers Part Number	FO32/V35/ECO/22437
UPC	046135224379

### Taxonomies, Classifications, and Categories

Category Description	Fluorescent
Type	FLUORESCENT

### Packaging

Carton	1
Package	30
Weight Per each	0.4207