

FEATURES & SPECIFICATIONS

INTENDED USE

Floodlights for commercial or residential signs, entry monuments or facades.

CONSTRUCTION

Rugged, die-cast aluminum housing constructed for maximum heat dissipation. Die-cast aluminum door frames.

Dark bronze housing. Anodized aluminum reflectors with high efficiency and wide beam spread.¹ Tempered glass lens with high temperature gasket to inhibit entrance of contaminants. Micro and small floodlights feature adjustable mounting knuckle with 1/2" NPS threaded stem; medium flood is yoke mount.

ELECTRICAL

120V reactor, normal power factor for 50-150W HPS and 70-100W MH. Quad-tap, high-reactance, high power factor ballast for 150W MH. Medium-base socket. Quad-tap, super CWA, pulse start ballasts are 88% efficient and EISA compliant for 250W and 400W MH. Mogul-base socket.

LISTING

UL Listed (standard). CSA Certified (see Options). UL listed for wet locations.

WARRANTY

Fixtures are covered by Lithonia Lighting 24-month warranty against mechanical defects in manufacture.

Note: Specifications subject to change without notice.

Catalog Number
Notes
Type

Contractor Select

Flood Lighting



F50-150




F150M




F250-400


50-150W High Pressure Sodium
70-400W Metal Halide



F50-150 Micro



F150M Small



F250-400 Medium

All dimensions are inches (centimeters).

ORDERING INFORMATION

Catalog Number	UPC	Description	Wattage	Lamp Source	Voltage	NEMA Distribution	Lamp Included	Approx. Weight (lbs)	Pallet Qty	Standard Carton Qty
F50SL 120 M6	745973505496	Micro floodlight	50	HPS	120	--	Y	7	144	6
F70SL 120 M6	745973505441	Micro floodlight	70	HPS	120	--	Y	7	180	6
F100SL 120 M6	745973505502	Micro floodlight	100	HPS	120	--	Y	7	144	6
F150SL 120 M6	745973505380	Micro floodlight	150	HPS	120	6x6	Y	7	180	6
F70ML 120 M6	745973505489	Micro floodlight	70	MH	120	--	Y	7	144	6
F100ML 120 M6	745973817872	Micro floodlight	100	MH	120	--	Y	7	144	6
F150ML M4	745975146208	Small floodlight	150	MH	120/208/240/277	7x7	Y	14	64	4
F150MSL M4	745975146444	Small floodlight (spot)	150	MH	120/208/240/277	5x4	Y	14	64	4
F250ML SCWA	745975145126	Medium floodlight	250 ²	MH	120/208/240/277	7x6	Y	29	20	1
F400ML SCWA	745975145195	Medium floodlight	400 ²	MH	120/208/240/277	7x6	Y	29	20	1

Notes

- F150MSL features spot distribution.
- These wattages do not comply with California Title 20 regulations.

