



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## F15T8CW 15W T8 18" Cool White 62 Cri Bi-Pin Fluor Lamp

*Sylvania-Ledvance*

Catalog Number	F15T8CW
Manufacturer	Sylvania-Ledvance
Description	15W T8 Preheat Fluorescent Lamp, Cool White Phosphor, 4200K Color Temperature, 60 Cri. 7500 Avg Rated Life At 3 HRS/Start
Weight per unit	0.1900 (lbs/each)
Product Category	Linear Fluorescent Straight La

### Features

amperage rating	Ballast Dependent
Base	Medium Bipin
Lamp Type	PREHEAT
lumens	825 Initial Lumens at 25 Degrees C
Shape	T8
start type	PREHEAT
total harmonic distortion	Ballast Dependent
Voltage Rating	Ballast Dependent

### Material, Color, and Finish

color rendering index (cri)	60
color temperature	4200

### Descriptions

Description	15W T8 18" COOL WHITE 62 CRI BI-PIN FLUOR LAMP
extra long description	SYL F15T8CW/21616 F15T8CW 24/CS 1/S
Long Description	15W T8 preheat fluorescent lamp, Cool White phosphor, 4200K color temperature, 60 CRI. 7500 Avg rated life at 3 hrs/start
Special Features	COOL WHITE

### Manufacturer Information

Brand	SYLVANIA
GTIN	00046135216169
Manufacturers Part Number	F15T8/CW/21616
UPC	046135216169

### Taxonomies, Classifications, and Categories

Category Description	Fluorescent
Type	FLUORESCENT



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	1
Package	24
Weight Per each	0.19

## Uses, Certifications, and Standards

Application	Commercial/Residential
-------------	------------------------