



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## F17T8SP41ECO 17W T8 24" 4100K 78 Cri Bi Pin Energy Saving

*Ge By Current Lamps*

Catalog Number	F17T8SP41ECO
Manufacturer	Ge By Current Lamps
Description	Fluorescent Lamp, G13 Medium Bi-Pin Base, T8 Bulb Shape, 78, 30000 H Average Life, 4100 K, 70 V, 17 W, 1325 LM Brightness (Lumens), Soda Lime Housing Material, 1.0 In Diameter, 24.0 In Length, Instant;Rapid, 0.26 LB
Weight per unit	0.2600 (lbs/each)
Product Category	Linear Fluorescent Straight La

### Features

Base	Medium Bi-Pin (G13)
lumens	1325.0
Wattage	17.0

### Material, Color, and Finish

color rendering index (cri)	78.0
-----------------------------	------

### Descriptions

Description	17W T8 24" 4100K 78 CRI BI PIN ENERGY SAVING
extra long description	GEL F17T8/SP41/ECO 45748 FLUORESCEN

### Manufacturer Information

Brand	Ge Traditional Lamps
GTIN	00043168457484
UPC	043168457484

### Taxonomies, Classifications, and Categories

Category Description	Fluorescent
----------------------	-------------

### Packaging

Carton	1
Package	24
Weight Per each	0.26