



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

4712 E Highland Dr  
72401-0000, AR Jonesboro  
Phone: 870-604-1924  
Fax: 870-497-2677



## F20T12CW 20W T12 24" Cool White 62 Cri Bi-Pin Fluor Lamp

*Ge By Current Lamps*

Catalog Number	F20T12CW
Manufacturer	Ge By Current Lamps
Description	Ge Ecolux®, 20 WTT, 1200 LM, 4100 KV, 60 Cri, 1.5 In Diameter, 24 In Length, Medium Bi-Pin (G13) Base, 9000 HR Average Life
Weight per unit	0.3600 (lbs/each)
Product Category	Linear Fluorescent Straight La

### Features

average life	9000
Base	Medium Bi-Pin (G13)
lumens	1200
Wattage	20

### Material, Color, and Finish

color rendering index (cri)	60.0
color temperature	4100.0

### Dimensions and Weight

Diameter	1.5
Length	24

### Descriptions

Description	20W T12 24" COOL WHITE 62 CRI BI-PIN FLUOR LAMP
extra long description	GEL F20T12/CW/ECO 80045 SLIM LINE /
Long Description	GE Ecolux®, 20 WTT, 1200 LM, 4100 KV, 60 CRI, 1.5 IN Diameter, 24 IN Length, Medium Bi-Pin (G13) Base, 9000 HR Average Life
Product Type	80045 Slim Line / F20

### Manufacturer Information

Brand	Ge Traditional Lamps
GTIN	00043168800457
Manufacturers Part Number	F20T12/CW/ECO
UPC	043168800457

### Taxonomies, Classifications, and Categories

Category Description	Fluorescent
----------------------	-------------

### Availability

Status	Inactive
--------	----------

### Packaging

Carton	1
Package	24
Weight Per each	0.36



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

4712 E Highland Dr  
72401-0000, AR Jonesboro  
Phone: 870-604-1924  
Fax: 870-497-2677

---

## Uses, Certifications, and Standards

Application .....

Full Wattage .....