



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

F30T12CWRS 30W T12 36" Cool White 60 Cri Bi-Pin Rapid Start

Sylvania-Ledvance

Catalog Number	F30T12CWRS
Manufacturer	Sylvania-Ledvance
Description	30W, T12 Rapid Start Fluorescent Lamp, Cool White Phosphor, 4200K Color Temperature, 60 Cri, 18000 Avg Rated Life At 3 HRS/Start
Weight per unit	0.6600 (lbs/each)
Product Category	Linear Fluorescent Straight La

Features

amperage rating	Ballast Dependent
average life	18000
Base	Medium Bipin
Lamp Type	RAPID START
lumens	2200 Initial Lumens at 25 Degrees C
Shape	T12
start type	Rapid Start
total harmonic distortion	Ballast Dependent
Voltage Rating	Ballast Dependent
Wattage	30

Material, Color, and Finish

color rendering index (cri)	60
color temperature	4200
Finish	Phosphor Coated

Dimensions and Weight

Diameter	1.5 in
----------	--------

Descriptions

Description	30W T12 36" COOL WHITE 60 CRI BI-PIN RAPID START
extra long description	SYL F30T12/CW/RS/23476 F30T12CWRS 3
Long Description	30W, T12 rapid start fluorescent lamp, Cool White phosphor, 4200K color temperature, 60 CRI, 18000 Avg rated life at 3 hrs/start
Product Type	F30T12CWRS 30/CS 1/Sku
Special Features	COOL WHITE

Manufacturer Information

Brand	SYLVANIA
GTIN	00046135234767
Manufacturers Part Number	F30T12/CW/RS/23476
UPC	046135234767



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description	Fluorescent
Type	FLUORESCENT

Packaging

Carton	1
Package	30
Weight Per each	0.66

Uses, Certifications, and Standards

Application	Commercial/Residential
-------------	------------------------