



F32T8/835K



| | |
|----------------------|--|
| Description | 32W Universal Start 3500K 85 CRI T-8 Medium Bi-pin |
| Ordering Code | 49588 |
| UNSPSC Code | 39101605 |

Specifications

| | |
|----------------------------------|---------------------------------|
| Watts | 32 |
| Base Type | G13 |
| Bulb Type | T-8 |
| MOL in/mm | 48.0/1219 |
| Length | 4' |
| MOD in/mm | 1.0/26 |
| Approx Initial Lumens | 2950 |
| Approx Mean Lumens | 2800 |
| CT deg K | 3500 |
| CRI | 85 |
| Avg Life 3 HR Inst Start | 24000 |
| Avg Life 3 HR Prog Start | 30000 |
| Avg Life 12 HR Inst Start | 30000 |
| Avg Life 12 HR Prog Start | 36000 |
| Special Desc | Three Phosphor, Universal Start |

watch > like > follow



selection. solutions. simplicity. eiko.com

23220 W. 84th St, Shawnee, KS 66227 · (P) 1.800.852.2217 (F) 1.800.492.8975

Canada: 81 King St, Barrie, ON L4N 6B5 · (P) 1.888.410.8151 (F) 1.888.705.1335



F32T8/835K



| | |
|----------------------|--|
| Description | 32W Universal Start 3500K 85 CRI T-8 Medium Bi-pin |
| Ordering Code | 49588 |
| UNSPSC Code | 39101605 |

Specifications

| | |
|----------------------------------|---------------------------------|
| Watts | 32 |
| Base Type | G13 |
| Bulb Type | T-8 |
| MOL in/mm | 48.0/1219 |
| Length | 4' |
| MOD in/mm | 1.0/26 |
| Approx Initial Lumens | 2950 |
| Approx Mean Lumens | 2800 |
| CT deg K | 3500 |
| CRI | 85 |
| Avg Life 3 HR Inst Start | 24000 |
| Avg Life 3 HR Prog Start | 30000 |
| Avg Life 12 HR Inst Start | 30000 |
| Avg Life 12 HR Prog Start | 36000 |
| Special Desc | Three Phosphor, Universal Start |

watch > like > follow



selection. solutions. simplicity. eiko.com

23220 W. 84th St, Shawnee, KS 66227 · (P) 1.800.852.2217 (F) 1.800.492.8975

Canada: 81 King St, Barrie, ON L4N 6B5 · (P) 1.888.410.8151 (F) 1.888.705.1335