



GE
Lighting

63548 - F32T8/841/PRO/EC

F32T8/841/PRO/EC



GENERAL CHARACTERISTICS

Lamp Type	Linear Fluorescent - Straight
	Linear
Bulb	T8
Base	Medium Bi-Pin (G13)
Rated Life (NOM)	20000.0 h
Bulb Material	Sodalime glass
Starting Temperature (MIN)	10.0 °C
Mercury Content (NOM)	2.95 mg
Picograms of Mercury (NOM)	53.64612 pg
Primary Application	Full Wattage

PHOTOMETRIC CHARACTERISTICS

Initial Lumens (NOM)	2925.0
Nominal Initial Lumens per Watt (NOM)	91.40625
Color Temperature (NOM)	4100.0 K
Color Rendering Index (CRI) (NOM)	85.0

ELECTRICAL CHARACTERISTICS

Wattage (NOM)	32.0
---------------	------

DIMENSIONS

Maximum Overall Length (MOL) (NOM)	48.000 in(1219.2 mm)
Nominal Length (NOM)	48.000 in(1219.2 mm)
Bulb Diameter (DIA) (NOM)	1.000 in(25.4 mm)

PRODUCT INFORMATION

Product Code	63548
Description	F32T8/841/PRO/EC
Standard Package	00-Case
Standard Package GTIN	10043168635483
Standard Package Quantity	36
Sales Unit	Unit
No Of Items Per Sales Unit	1
No Of Items Per Standard Package	36
UPC	043168635486



GE
Lighting

63548 - F32T8/841/PRO/EC

F32T8/841/PRO/EC



GENERAL CHARACTERISTICS

Lamp Type	Linear Fluorescent - Straight
	Linear
Bulb	T8
Base	Medium Bi-Pin (G13)
Rated Life (NOM)	20000.0 h
Bulb Material	Sodalime glass
Starting Temperature (MIN)	10.0 °C
Mercury Content (NOM)	2.95 mg
Picograms of Mercury (NOM)	53.64612 pg
Primary Application	Full Wattage

PHOTOMETRIC CHARACTERISTICS

Initial Lumens (NOM)	2925.0
Nominal Initial Lumens per Watt (NOM)	91.40625
Color Temperature (NOM)	4100.0 K
Color Rendering Index (CRI) (NOM)	85.0

ELECTRICAL CHARACTERISTICS

Wattage (NOM)	32.0
---------------	------

DIMENSIONS

Maximum Overall Length (MOL) (NOM)	48.000 in(1219.2 mm)
Nominal Length (NOM)	48.000 in(1219.2 mm)
Bulb Diameter (DIA) (NOM)	1.000 in(25.4 mm)

PRODUCT INFORMATION

Product Code	63548
Description	F32T8/841/PRO/EC
Standard Package	00-Case
Standard Package GTIN	10043168635483
Standard Package Quantity	36
Sales Unit	Unit
No Of Items Per Sales Unit	1
No Of Items Per Standard Package	36
UPC	043168635486