



GE  
Lighting

66351 - F32T8/SPP65/ECO

F32T8/SPP65/ECO

#### GENERAL CHARACTERISTICS

Base Description	Medium Bi-Pin
Base Type	Pin/Plug-In
Mercury Content	2.95 mg
Mercury-Picogram per mean lm hr	36.1
Rated Life Instant Start-Hrs	21000 h @ 3 h 30000 h @ 12 h
Rated Life Rapid Start - Hrs	30000 h @ 3 h 36000 h @ 12 h
Bulb Material	Sodalime glass
Rated Life Hours-nominal	30000 h
Primary Application	Full Wattage
Product Technology	Linear Fluorescent
Base	G13
Bulb Shape	T8

#### PHOTOMETRIC CHARACTERISTICS

Mean Lumens nominal	2725 lm
Nominal Initial Lumen per Watt	91
Initial Lumens-nominal	2900 lm
Color Rendering Index-CRI	80
Color Temperature	6500 K

#### PRODUCT INFORMATION

Product Code	66351
Description	F32T8/SPP65/ECO
Alternative Unit Of Measure	00-Case
Standard Package Quantity	36
Ean UPC	043168663519
Standard Package GTIN	10043168663516
No Of Items Per Sales Unit	1
No Of Items Per Standard Package	36
Sales Unit	Unit
UCC	043168663519

#### DIMENSIONS

Diameter	1 in
Nominal Length	48 in

#### ELECTRICAL CHARACTERISTICS

Rated power (Watts)	32 W
---------------------	------



GE  
Lighting

66351 - F32T8/SPP65/ECO

F32T8/SPP65/ECO

#### GENERAL CHARACTERISTICS

Base Description	Medium Bi-Pin
Base Type	Pin/Plug-In
Mercury Content	2.95 mg
Mercury-Picogram per mean lm hr	36.1
Rated Life Instant Start-Hrs	21000 h @ 3 h 30000 h @ 12 h
Rated Life Rapid Start - Hrs	30000 h @ 3 h 36000 h @ 12 h
Bulb Material	Sodalime glass
Rated Life Hours-nominal	30000 h
Primary Application	Full Wattage
Product Technology	Linear Fluorescent
Base	G13
Bulb Shape	T8

#### PHOTOMETRIC CHARACTERISTICS

Mean Lumens nominal	2725 lm
Nominal Initial Lumen per Watt	91
Initial Lumens-nominal	2900 lm
Color Rendering Index-CRI	80
Color Temperature	6500 K

#### PRODUCT INFORMATION

Product Code	66351
Description	F32T8/SPP65/ECO
Alternative Unit Of Measure	00-Case
Standard Package Quantity	36
Ean UPC	043168663519
Standard Package GTIN	10043168663516
No Of Items Per Sales Unit	1
No Of Items Per Standard Package	36
Sales Unit	Unit
UCC	043168663519

#### DIMENSIONS

Diameter	1 in
Nominal Length	48 in

#### ELECTRICAL CHARACTERISTICS

Rated power (Watts)	32 W
---------------------	------