



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



F32T8SPX41ECOCVG 32W T8 Coated 48" 4100K Med Bi-Pin Fluor Lamp

Ge By Current Lamps

Catalog Number	F32T8SPX41ECOCVG
Manufacturer	Ge By Current Lamps
Description	Ge Covrguard®, 32 WTT, 2860 LM, 4100 KV, 85 Cri, 1 In Diameter, 47.78 In Length, Medium Bi-Pin (G13) Base, 30000 HR Average Life
Weight per unit	0.4400 (lbs/each)
Product Category	Shatter Resistant Fluorescent

Features

average life	30000.0
Base	Medium Bi-Pin (G13)
lumens	2860.0
Wattage	32.0

Material, Color, and Finish

color rendering index (cri)	85.0
color temperature	4100.0

Dimensions and Weight

Diameter	1.0
Length	47.78

Descriptions

Description	32W T8 COATED 48" 4100K MED BI-PIN FLUOR LAMP
extra long description	GEL F32T8SPX41ECOCVG 41127 SLIM LIN
Long Description	GE covRguard®, 32 WTT, 2860 LM, 4100 KV, 85 CRI, 1 IN Diameter, 47.78 IN Length, Medium Bi-Pin (G13) Base, 30000 HR Average Life
Product Type	41127 Slim Line / F20

Manufacturer Information

Brand	Ge Traditional Lamps
GTIN	00043168411271
Manufacturers Part Number	F32T8SPX41ECOCVG
UPC	043168411271

Taxonomies, Classifications, and Categories

Category Description	Fluorescent
----------------------	-------------

Packaging

Carton	1
Package	36
Weight Per each	0.44



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application

Shatter-Resistant