



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



F32T8SPX50ECOCVG 32W T8 Coated Lamp 48" 5000K Med Bi-Pin Fluor Lamp

Ge By Current Lamps

Catalog Number	F32T8SPX50ECOCVG
Manufacturer	Ge By Current Lamps
Description	Ge Covrguard®, 32 WTT, 2715 LM, 5000 KV, 82 Cri, 1 In Diameter, 48 In Length, Medium Bi-Pin (G13) Base, 30000 HR Average Life
Weight per unit	0.5600 (lbs/each)
Product Category	Linear Fluorescent Straight La

Features

average life	30000.0
Base	Medium Bi-Pin (G13)
lumens	2715.0
Wattage	32.0

Material, Color, and Finish

color rendering index (cri)	82.0
color temperature	5000.0

Dimensions and Weight

Diameter	1.0
Length	48.0

Descriptions

Description	32W T8 COATED LAMP 48" 5000K MED BI-PIN FLUOR LAMP
extra long description	GEL F32T8SPX50ECOCVG 15971 SLIM L
Long Description	GE covRguard®, 32 WTT, 2715 LM, 5000 KV, 82 CRI, 1 IN Diameter, 48 IN Length, Medium Bi-Pin (G13) Base, 30000 HR Average Life
Product Type	15971 Slim Line / F20

Manufacturer Information

Brand	Ge Traditional Lamps
GTIN	00043168159715
Manufacturers Part Number	F32T8SPX50ECOCVG
UPC	043168159715

Taxonomies, Classifications, and Categories

Category Description	Fluorescent
----------------------	-------------

Packaging

Carton	1
Package	36
Weight Per each	0.56

Uses, Certifications, and Standards

Application	Shatter-Resistant
-------------	-------------------