



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## F32T8SPX50ECOCVG 32W T8 Coated Lamp 48" 5000K Med Bi-Pin Fluor Lamp

*Ge By Current Lamps*

Catalog Number	F32T8SPX50ECOCVG
Manufacturer	Ge By Current Lamps
Description	Ge Covrguard®, 32 WTT, 2715 LM, 5000 KV, 82 Cri, 1 In Diameter, 48 In Length, Medium Bi-Pin (G13) Base, 30000 HR Average Life
Weight per unit	0.5600 (lbs/each)
Product Category	Linear Fluorescent Straight La

### Features

average life	30000.0
Base	Medium Bi-Pin (G13)
lumens	2715.0
Wattage	32.0

### Material, Color, and Finish

color rendering index (cri)	82.0
color temperature	5000.0

### Dimensions and Weight

Diameter	1.0
Length	48.0

### Descriptions

Description	32W T8 COATED LAMP 48" 5000K MED BI-PIN FLUOR LAMP
extra long description	GEL F32T8SPX50ECOCVG 15971 SLIM L
Long Description	GE covRguard®, 32 WTT, 2715 LM, 5000 KV, 82 CRI, 1 IN Diameter, 48 IN Length, Medium Bi-Pin (G13) Base, 30000 HR Average Life
Product Type	15971 Slim Line / F20

### Manufacturer Information

Brand	Ge Traditional Lamps
GTIN	00043168159715
Manufacturers Part Number	F32T8SPX50ECOCVG
UPC	043168159715

### Taxonomies, Classifications, and Categories

Category Description	Fluorescent
----------------------	-------------

### Packaging

Carton	1
Package	36
Weight Per each	0.56

### Uses, Certifications, and Standards

Application	Shatter-Resistant
-------------	-------------------