



GE  
Lighting

**66649 - F34/CW/CWM/ECO**

F34/CW/CWM/ECO-LFL - 30PK WITH UPC STICKERS ON L



**GENERAL CHARACTERISTICS**

Lamp Type	Linear Fluorescent - Straight
	Linear
Bulb	T12
Base	Medium Bi-Pin (G13)
Rated Life	15000.0 hrs
Bulb Material	Sodalime glass
Starting Temperature (MIN)	15.0 °C
LEED-EB MR Credit	222 picograms Hg per mean lumen hour
Primary Application	Energy Saving

**PHOTOMETRIC CHARACTERISTICS**

Initial Lumens	1800.0
Mean Lumens	1500.0
Nominal Initial Lumens per Watt	52
Color Temperature	4100.0 K
Color Rendering Index (CRI)	87.0

**ELECTRICAL CHARACTERISTICS**

Wattage	34.0
---------	------

**DIMENSIONS**

Maximum Overall Length (MOL)	48.0000 in(1219.2 mm)
Nominal Length	48.000 in(1219.2 mm)
Bulb Diameter (DIA)	1.500 in(38.1 mm)

**PRODUCT INFORMATION**

Product Code	66649
Description	F34/CW/CWM/ECO
Standard Package	Case
Standard Package GTIN	10043168666494
Standard Package Quantity	30
Sales Unit	Unit
No Of Items Per Sales Unit	1
No Of Items Per Standard Package	30
UPC	043168666497



GE  
Lighting

**66649 - F34/CW/CWM/ECO**

F34/CW/CWM/ECO-LFL - 30PK WITH UPC STICKERS ON L



**GENERAL CHARACTERISTICS**

Lamp Type	Linear Fluorescent - Straight
	Linear
Bulb	T12
Base	Medium Bi-Pin (G13)
Rated Life	15000.0 hrs
Bulb Material	Sodalime glass
Starting Temperature (MIN)	15.0 °C
LEED-EB MR Credit	222 picograms Hg per mean lumen hour
Primary Application	Energy Saving

**PHOTOMETRIC CHARACTERISTICS**

Initial Lumens	1800.0
Mean Lumens	1500.0
Nominal Initial Lumens per Watt	52
Color Temperature	4100.0 K
Color Rendering Index (CRI)	87.0

**ELECTRICAL CHARACTERISTICS**

Wattage	34.0
---------	------

**DIMENSIONS**

Maximum Overall Length (MOL)	48.0000 in(1219.2 mm)
Nominal Length	48.000 in(1219.2 mm)
Bulb Diameter (DIA)	1.500 in(38.1 mm)

**PRODUCT INFORMATION**

Product Code	66649
Description	F34/CW/CWM/ECO
Standard Package	Case
Standard Package GTIN	10043168666494
Standard Package Quantity	30
Sales Unit	Unit
No Of Items Per Sales Unit	1
No Of Items Per Standard Package	30
UPC	043168666497