Elliott Electric Supply

We Deliver...Lower Cost, Quality Products, & Personal Service

6510 Broadway St
77554-0000, TX Galveston
Phone: 409-741-0072
Fax: 409-741-0433



F36T12CW Lamp F36T12/CW (Di)

Sylvania-Ledvance

Catalog Number	F36T12CW
Manufacturer	Sylvania-Ledvance
Description	OBS23618 30W, 36" Mol, T12 Instant Start Slimline Fluorescent Lamp, Cool White Phosphor, 4200K Color Temperature, 60 Cri
Weight per unit	0.5200 (lbs/each)
Product Category	Lighting

Features

amperage rating	Ballast Dependent
average life	7500
Base	Single Pin
lumens	1970 Initial Lumens at 25 Degrees C
Shape	T12
start type	Instant Start
total harmonic distortion	Ballast Dependent
Voltage Rating	Ballast Dependent
Wattage	30

Material, Color, and Finish

color rendering index (cri)	60
color temperature	4200
Finish	Phosphor Coated

Dimensions and Weight

Diameter	1.5 in

Descriptions

Description	LAMP F36T12/CW (DI)
extra long description	SYL F36T12/CW/23618 F36T12CW 30/CS
Long Description	OBS23618 30W, 36" MOL, T12 instant start Slimline fluorescent lamp, Cool White phosphor, 4200K color temperature, 60 CRI
Product Type	F36T12CW 30/CS 1/Sku
Special Features	COOL WHITE

Manufacturer Information

Brand	SYLVANIA
GTIN	00046135236181
Manufacturers Part Number	F36T12/CW/23618
UPC	046135236181

ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
6510 Broadway St
77554-0000, TX Galveston
Phone: 409-741-0072
Fax: 409-741-0433

Taxonomies, Classifications, and Categories

Category Description	Fluorescent
Type	FLUORESCENT

Packaging

Carton	1
Weight Per each	0.52

Uses, Certifications, and Standards

Application	Commercial/Residential