



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## F40C50ECO 40W T12 48" 5000K 90 Cri Bi-Pin Fluorescent

*Ge By Current Lamps*

Catalog Number	F40C50ECO
Manufacturer	Ge By Current Lamps
Description	Ge Ecolux®, 40 WTT, 2250 LM, 5000 KV, 90 Cri, 1.5 In Diameter, 48 In Length, Medium Bi-Pin (G13) Base, 20000 HR Average Life
Weight per unit	0.4100 (lbs/each)
Product Category	Linear Fluorescent Straight La

### Features

average life	20000.0
Base	Medium Bi-Pin (G13)
lumens	2250.0
Wattage	40.0

### Material, Color, and Finish

color rendering index (cri)	90.0
color temperature	5000.0

### Dimensions and Weight

Diameter	1.5
Length	48.0

### Descriptions

Description	40W T12 48" 5000K 90 CRI BI-PIN FLUORESCENT
extra long description	GEL F40C50/ECO 80096 FLUORESCENT F4
Long Description	GE Ecolux®, 40 WTT, 2250 LM, 5000 KV, 90 CRI, 1.5 IN Diameter, 48 IN Length, Medium Bi-Pin (G13) Base, 20000 HR Average Life
Product Type	80096 Fluorescent F40

### Manufacturer Information

Brand	Ge Traditional Lamps
GTIN	00043168800969
Manufacturers Part Number	F40C50/ECO
UPC	043168800969

### Taxonomies, Classifications, and Categories

Category Description	Fluorescent
----------------------	-------------

### Packaging

Carton	1
Package	30
Weight Per each	0.41

### Uses, Certifications, and Standards

Application	Full Wattage
-------------	--------------