



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1105 West Sanger  
88240-0000, NM Hobbs  
Phone: 575-397-2122  
Fax: 575-397-2178

## F40CWX 40W T12 48" 41K 87cri

*Sylvania-Ledvance*

Catalog Number	F40CWX
Manufacturer	Sylvania-Ledvance
Description	40W, T12 Rapid Start Fluorescent Lamp, Deluxe Cool White Phosphor, 4100K Color Temperature, 87 Cri. 20000 Avg Rated Life At 3 HRS/Start, 28800 Avg Rated Life At 12 HRS/Start. Vivid Color: High Cri Lamps For Color Critical Applications.
Weight per unit	0.6700 (lbs/each)
Product Category	Linear Fluorescent Straight La

### Features

amperage rating	Ballast Dependent
Base	Medium Bipin
bulb type	T12
Lamp Type	RAPID START
lumens	2150 Initial Lumens at 25 Degrees C
Shape	T12
total harmonic distortion	Ballast Dependent
Voltage Rating	Ballast Dependent
Wattage	40

### Material, Color, and Finish

color rendering index (cri)	87
color temperature	4100

### Descriptions

Description	40W T12 48" 41K 87CRI
extra long description	SYL F40CWX/24441 F40CWX 30/CS 1/SKU
Long Description	40W, T12 rapid start fluorescent lamp, Deluxe Cool White phosphor, 4100K color temperature, 87 CRI. 20000 Avg rated life at 3 hrs/start, 28800 Avg rated life at 12 hrs/start. VIVID Color: High CRI lamps for color critical applications.
Special Features	COOL WHITE

### Manufacturer Information

Brand	SYLVANIA
GTIN	00046135244414
Manufacturers Part Number	F40CWX/24441
UPC	046135244414

### Taxonomies, Classifications, and Categories

Category Description	Fluorescent
Type	FLUORESCENT



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1105 West Sanger  
88240-0000, NM Hobbs  
Phone: 575-397-2122  
Fax: 575-397-2178

## Packaging

Carton	1
Package	30
Weight Per each	0.67

## Uses, Certifications, and Standards

Application	Commercial/Residential
-------------	------------------------