



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## F40DSGN50 40W T12 48" 5000K 90 Cri Bi-Pin Fluorescent

*Sylvania-Ledvance*

Catalog Number	F40DSGN50
Manufacturer	Sylvania-Ledvance
Description	40W, T12 Rapid Start Fluorescent Lamp, DSGN 50 Phosphor, 5000K Color Temperature, 90 Cri. 20000 Avg Rated Life At 3 HRS/Start, 28800 Avg Rated Life At 12 HRS/Start. Vivid Color: High Cri Lamps For Color Critical Applications.
Weight per unit	0.6500 (lbs/each)
Product Category	Linear Fluorescent Straight La

### Features

amperage rating	Ballast Dependent
average life	20000
Base	Medium Bipin
Lamp Type	RAPID START
lumens	2200
Shape	T12
start type	RAPID START/PREHEAT
total harmonic distortion	Ballast Dependent
Voltage Rating	Ballast Dependent
Wattage	40

### Material, Color, and Finish

color rendering index (cri)	90
color temperature	5000
Finish	Phosphor Coated

### Dimensions and Weight

Diameter	1.5 in
Length	47.78

### Descriptions

Description	40W T12 48" 5000K 90 CRI BI-PIN FLUORESCENT
extra long description	SYL F40DSGN50/24683 F40DSGN50 30/CS
Long Description	40W, T12 rapid start fluorescent lamp, DSGN 50 phosphor, 5000K color temperature, 90 CRI. 20000 Avg rated life at 3 hrs/start, 28800 Avg rated life at 12 hrs/start. VIVID Color: High CRI lamps for color critical applications.
Product Type	F40DSGN50 30/CS 1/Sku

### Manufacturer Information

Brand	SYLVANIA
GTIN	00046135246838
Manufacturers Part Number	F40DSGN50/24683
UPC	046135246838



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Taxonomies, Classifications, and Categories

Category Description ..... Fluorescent

Type ..... FLUORESCENT

## Packaging

Carton ..... 1

Package ..... 30

Weight Per each ..... 0.65

## Uses, Certifications, and Standards

Application ..... Commercial/Residential