



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## F40DX 40W T12 48" 6500K 88CRI By-Bin Daylight Rapid Star

*Sylvania-Ledvance*

Catalog Number	F40DX
Manufacturer	Sylvania-Ledvance
Description	40W, T12 Rapid Start Fluorescent Lamp, Daylight Deluxe Phosphor, 6500K Color Temperature, 88 Cri. 20000 Avg Rated Life At 3 HRS/Start, 28800 Avg Rated Life At 12 HRS/Start. Vivid Color: High Cri Lamps For Color Critical Applications
Weight per unit	0.6670 (lbs/each)
Product Category	Linear Fluorescent Straight La

### Features

amperage rating	Ballast Dependent
Base	Medium Bipin
beam angle	Universal
bulb type	T12
Lamp Type	RAPID START
lumens	2180 Initial Lumens at 25 Degrees C
Shape	T12
total harmonic distortion	Ballast Dependent
Voltage Rating	Ballast Dependent
Wattage	40

### Material, Color, and Finish

color rendering index (cri)	88
color temperature	6500

### Descriptions

Description	40W T12 48" 6500K 88CRI BY-BIN DAYLIGHT RAPID STAR
extra long description	SYL F40DX/24477 F40DX 30/CS 1/SKU
Long Description	40W, T12 rapid start fluorescent lamp, Daylight Deluxe phosphor, 6500K color temperature, 88 CRI. 20000 Avg rated life at 3 hrs/start, 28800 Avg rated life at 12 hrs/start. VIVID Color: High CRI lamps for color critical applications

### Manufacturer Information

Brand	SYLVANIA
GTIN	00046135244773
Manufacturers Part Number	F40/DX/24477
UPC	046135244773

### Taxonomies, Classifications, and Categories

Category Description	Fluorescent
Type	FLUORESCENT



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton ..... 30

Weight Per each ..... 0.667

## Uses, Certifications, and Standards

Application ..... Commercial/Residential

standard ..... ANSI C78.81 - 2001