ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
Nacogdoches, TX 75964-0
Phone: 9365697941
Fax: 9365604685



F40DXEC0 40W T12 48" 6500K 90CRI BI PIN FLUORESCENT LAMP

GE BY CURRENT LAMPS

Catalog Number	F40DXEC0
Manufacturer	GE BY CURRENT LAMPS
Description	GE Ecolux®, 40 WTT, 2050 LM, 6500 KV, 90 CRI, 1.5 IN Diameter, 48 IN Length, Medium Bi-Pin (G13) Base, 20000 HR Average Life
Weight per unit	0.6700 (lbs/each)
Product Category	Linear Fluorescent Straight La

Features

Base	Medium Bi-Pin (G13)
Wattage	40
Average Life	20000
Lumens	2050

Material, Color, and Finish

Color Rendering Index (Cri)	90.0
Color Temperature	6500.0

Dimensions and Weight

Diameter	1.5
Length	48

Descriptions

Description	40W T12 48" 6500K 90CRI BI PIN FLUORESCENT LAMP
Long Description	GE Ecolux®, 40 WTT, 2050 LM, 6500 KV, 90 CRI, 1.5 IN Diameter, 48 IN Length, Medium Bi-Pin (G13) Base, 20000 HR Average Life
Product Type	80097 Fluorescent F40
Extra Long Description	GEL F40DX/ECO 80097 FLUORESCENT F40

Manufacturer Information

Brand	Current Lighting
	Ge Traditional Lamps
GTIN	00043168800976
UPC	043168

Taxonomies, Classifications, and Categories

Category Description	Fluorescent

Packaging

Carton	1
Package	30
Weight Per Each	0.6700 (lbs/each)

Uses, Certifications, and Standards

Application	Full Wattage