



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



F44G24WK 4X4X24 N1 STRT SCT HC, Ko *Hoffman Enclosures, Inc.*

Catalog Number	F44G24WK
Manufacturer	Hoffman Enclosures, Inc.
Description	Straight Section Lay-In Hinged-Cover Type 1 With Kos, 4X4X24, Gray, Steel
Weight per unit	28.3 (lbs/each)
Product Category	Nema Type 1 Wireway & Fittings

Features

ip rating	IP30
Knockouts	Yes
Material	MILD STEEL

Material, Color, and Finish

Color	Gray
Color Code	ANSI 61
Finish	Powder Coated
Style	Liftoff Cover with Knockouts

Dimensions and Weight

Height	4
Width	4

Descriptions

Description	4X4X24 N1 STRT SCT HC,KO
extra long description	NVENT HOF F44G24WK 24.00in Straight
Features	Lay-in Hinged-Cover Type 1 Straight Sections are used for enclosing wire and cable in wireway runs. Sections are completely open on one side so wires and cables can be laid in along wireway run. No pulling through of wires or cables prevents damage to insulation that often occurs in a pull-through wiring system. Sections are available in lengths from 12 inch to 120 inch, with or without knockouts.
Long Description	Straight Section Lay-in Hinged-Cover Type 1 with KOs, 4x4x24, Gray, Steel
Product Type	24.00IN Straight Section / Ko

Manufacturer Information

Brand	Nvent Hoffman
GTIN	00783510529109
Manufacturers Part Number	F44G24WK
UPC	783510529109



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description	STEEL WIRE WAY JUNCTION BOXES
Type	Straight Section

Packaging

Carton	1
Package	4
Weight Per each	28.32

Uses, Certifications, and Standards

Application	Power Distribution
nema rating	1 Indoor, electrical protection