



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

F48T12CWH0 60W T12 48" Cool White High Output 62 Cri R17D

Ge By Current Lamps

| | |
|------------------|--|
| Catalog Number | F48T12CWH0 |
| Manufacturer | Ge By Current Lamps |
| Description | Fluorescent Lamp, Recessed Double Contact R17D Base, T12 Bulb Shape, 60, 20000 H Average Life, 4100 K, Cool White, 60 W, 3825 LM Brightness (Lumens), Soda Lime Housing Material, 1.5 In Diameter, 48.0 In Length, Rapid, 0.68 LB/Ea |
| Weight per unit | 1.0 (lbs/each) |
| Product Category | Linear Fluorescent Straight La |

Features

| | |
|---------|--------------------------------|
| Base | Recessed Double Contact (R17d) |
| lumens | 3825.0 |
| Wattage | 60.0 |

Material, Color, and Finish

| | |
|-----------------------------|------|
| color rendering index (cri) | 60.0 |
|-----------------------------|------|

Dimensions and Weight

| | |
|----------|------|
| Diameter | 1.5 |
| Length | 48.0 |

Descriptions

| | |
|------------------------|--|
| Description | 60W T12 48" COOL WHITE HIGH OUTPUT 62 CRI R17D |
| extra long description | GEL F48T12/CW/HO 10773 FLUORESCENT |

Manufacturer Information

| | |
|-------|----------------------|
| Brand | Ge Traditional Lamps |
| GTIN | 00043168107730 |
| UPC | 043168107730 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|--------------------------|
| Category Description | HIGH VOLUME FLUORESCENTS |
|----------------------|--------------------------|

Packaging

| | |
|-----------------|------|
| Carton | 1 |
| Package | 24 |
| Weight Per each | 1.01 |