



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## F48T12CWHO 60W T12 48" Cool White High Output 62 Cri R17D

*Sylvania-Ledvance*

Catalog Number	F48T12CWHO
Manufacturer	Sylvania-Ledvance
Description	60W, 48" Mol, T12 Ho (800 Ma) Rapid Start Fluorescent Lamp, Cool White Phosphor, 4200K Color Temperature, 60 Cri.
Weight per unit	0.6800 (lbs/each)
Product Category	Linear Fluorescent Straight La

### Features

amperage rating	Ballast Dependent
Base	Recessed Double Contact
Lamp Type	RAPID START
lumens	4,050
Shape	T12
total harmonic distortion	Ballast Dependent
Voltage Rating	Ballast Dependent
Wattage	60

### Material, Color, and Finish

color rendering index (cri)	60
color temperature	4200

### Descriptions

Description	60W T12 48" COOL WHITE HIGH OUTPUT 62 CRI R17D
extra long description	SYL F48T12CWHO/25146 F48T12CWHO 30/
Long Description	60W, 48" MOL, T12 HO (800 mA) rapid start fluorescent lamp, Cool White phosphor, 4200K color temperature, 60 CRI.
Special Features	COOL WHITE

### Manufacturer Information

Brand	SYLVANIA
GTIN	00046135251467
Manufacturers Part Number	F48T12/CW/HO/25146
UPC	046135251467

### Taxonomies, Classifications, and Categories

Category Description	Fluorescent
Type	FLUORESCENT

### Packaging

Carton	1
Package	30
Weight Per each	0.68

### Uses, Certifications, and Standards

Application	Commercial/Residential
-------------	------------------------