



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

F48T12DH0 60W T12 48" Daylight High Output 76 Cri R17D

Sylvania-Ledvance

Catalog Number	F48T12DH0
Manufacturer	Sylvania-Ledvance
Description	60W, 48" Mol, T12 Ho (800 Ma) Rapid Start Fluorescent Lamp, Daylightphosphor, 6500K Color Temperature, 72 Cri
Weight per unit	0.6800 (lbs/each)
Product Category	Linear Fluorescent Straight La

Features

amperage rating	Ballast Dependent
average life	12000
Base	Recessed Double Contact
bulb type	T12
Lamp Type	RAPID START
lumens	3600 Initial Lumens at 25 Degrees C
Shape	T12
start type	Rapid Start
total harmonic distortion	Ballast Dependent
Voltage Rating	Ballast Dependent
Wattage	60

Material, Color, and Finish

color rendering index (cri)	76
color temperature	6500
Finish	Phosphor Coated

Dimensions and Weight

Diameter	1.5 in
----------	--------

Descriptions

Description	60W T12 48" DAYLIGHT HIGH OUTPUT 76 CRI R17D
extra long description	SYL F48T12DH0/25150 F48T12DH0 30/CS
Long Description	60W, 48" MOL, T12 HO (800 mA) rapid start fluorescent lamp, Daylightphosphor, 6500K color temperature, 72 CRI
Product Type	F48T12DH0 30/CS 1/Sku

Manufacturer Information

Brand	SYLVANIA
GTIN	00046135251504
Manufacturers Part Number	F48T12/D/HO/25150
UPC	046135251504



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description	Fluorescent
Type	FLUORESCENT

Packaging

Carton	1
Package	30
Weight Per each	0.68

Uses, Certifications, and Standards

Application	Commercial/Residential
-------------	------------------------