ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
1207 Energy Drive
75662-0000, TX Kilgore
Phone: 903-984-8485
Fax: 903-984-8193



F66G48WK 6X6X48 N1 HC STRT SCT

Hoffman Enclosures, Inc.

Catalog Number	F66G48WK
Manufacturer	Hoffman Enclosures, Inc.
Description	Straight Section Lay-In Hinged-Cover Type 1 With Kos, 6X6X48, Gray, Steel
Weight per unit	43.5 (lbs/each)
Product Category	Nema Type 1 Wireway & Fittings

Features

ip rating	IP30
Knockouts	true
Material	Mild Steel;Steel

Material, Color, and Finish

Color	Gray
Color Code	ANSI 61
Finish	Painted;Powder Coat
Style	Liftoff Cover with Knockouts

Dimensions and Weight

Height	6
Width	6

Descriptions

Description	6X6X48 N1 HC STRT SCT
extra long description	NVENT HOF F66G48WK 48.00in Straight
Features	Lay-in Hinged-Cover Type 1 Straight Sections are used for enclosing wire and cable in wireway runs. Sections are completely open on one side so wires and cables can be laid in along wireway run. No pulling through of wires or cables prevents damage to insulation that often occurs in a pull-through wiring system. Sections are available in lengths from 12 inch to 120 inch, with or without knockouts.
Long Description	Straight Section Lay-in Hinged-Cover Type 1 with KOs, 6x6x48, Gray, Steel
Product Type	48.00IN Straight Section / Ko
Short Description	48.00in Straight Section / KO

Manufacturer Information

Brand	Nvent Hoffman
GTIN	00783510529802
Manufacturers Part Number	F66G48WK
UPC	783510529802

ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
1207 Energy Drive
75662-0000, TX Kilgore
Phone: 903-984-8485
Fax: 903-984-8193

Taxonomies, Classifications, and Categories

Category Description	STEEL WIRE WAY JUNCTION BOXES
Type	Commercial Lay-in Hinged-Cover Type 1 Wireway;Straight Section

Packaging

Carton	1
Package	4
Weight Per each	43.5

Uses, Certifications, and Standards

Application	Power Distribution
nema rating	1